

## Liquidtight Flexible Cord & Cable Fittings

### T&B Catalog Number:



4960

**UPC Number:** 78621004960**Status:** Active**Description:**

1/2 in. 90 degree malleable iron Ranger liquidtight cord connector, cord range .125-.375

#### Features

Extended range with superior strain relief.

Reduced overall size, fits into tighter spaces.

Gland nut designed to restrict cable bending.

#### Application

Provide a means for passing a cord cable into an enclosure through a bulkhead

Suitable for Ordinary, Wet or Dry locations.

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

#### General

Material	Malleable Iron
Cord and Cable Types	S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

#### Dimension Information

Hub Size (inches)	1/2
Dimension A (inches)	1 1/8
Dimension B (inches)	1 3/4
Dimension C (inches)	5/8
Cord Range (inches)	.125-.375
Throat Diameter (inches)	19/32

#### Specifications

3dmodel	Available on Website
---------	----------------------

#### Packaging

T&B Inner Pack	25
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	24.9 lbs. per 100

#### Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

#### Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

#### Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E 13938

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)