

MATERIALS AND FINISHES




BODY AND COUPLUNG NUT STAINLESS STEEL
PASSIVATED

CENTER CONTACT BRASS
PLATED GOLD





INSULATOR TEFLON

CRIMP TUBE BRASS
PLATED NICKEL

SHRINK TUBE VERSIFIT OR EQUIVALENT



RECOMMENDED STRIP DIMENSIONS
CRIMP USING .213 HEX



SHRINK TUBE

73251-0112	ONE PIECE 73251-0111 PER BAG
73251-0111	BULK
PART NO.	PACKAGING

ES-89675-1570	CABLE ASSY INSTRUCT.
MIL-STD-348A, FIG. 310.1	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: CLARIFIED 1 PC PER BAG. EC NO: URF2010-0369 DRWN:AROBERTSON 2009/12/18 CHKD:SSS 2009/12/18 APPR: JWIENER 2009/12/18 A2	QUALITY SYMBOLS ▽=0 ▽=0 DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr></table> ANGULAR ± 2 °		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	DIMENSION STYLE MM/IN	SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE SMA PLUG, STR,CRIMP TYPE FOR RG55/142/223/400 SMA-PC
				mm	INCH																	
4 PLACES	± ---	± ---																				
3 PLACES	± ---	± ---																				
2 PLACES	± ---	± ---																				
1 PLACE	± ---	± ---																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWN BY GMH 1997/11/07 CHECKED BY DHG 1998/01/05 APPROVED BY GMH 1997/01/06 MATERIAL NO. SEE TABLE SIZE C				MOLEX INCORPORATED DOCUMENT NO. SD-73251-011 SHEET NO. 1 OF 1																	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						