


© AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN
© TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION
5 FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSONS OR ORGANIZATIONS WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Yellow		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278878-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6278878-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6278878-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6278878-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6278878-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6278878-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6278878-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6278878-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6278878-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6278878-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6278878-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6278878-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6278878-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6278878-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6278878-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6278878-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6278878-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6278878-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6278878-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6278878-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6278878-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6278878-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6278878-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6278878-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6278878-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6278878-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6278878-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6278878-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6278878-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6278878-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6278878-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6278878-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6278878-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6278878-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6278878-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6278878-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6278878-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6278878-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6278878-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6278878-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6278878-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Yellow	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
2	piece	SC Simplex Housing, Beige	9
2	piece	2.5mm ferrule cover	10
AR	meter	2 fiber, 50/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	SC Duplex Clip	13
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Trace Label	16

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B1	Rev Per EC#	MINOR REVISION	9/25/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

DIN Cable Assy Configurator

OK Michael Kepko

APVD Michael Kepko

MATERIAL -

HEAT TREAT -

Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE
(No Pins) to SC-Duplex

SCALE NTS

SIZE A2

DRAWING NO C- 6278878

SHEET 2 of 3

REV B1

8 7 6 5 4 3 2 1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B1	Rev Per EC#	MINOR REVISION	9/25/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters			
Ø	9 P.L.C.	±	-
□	1 P.L.C.	±	-
□	2 P.L.C.	±	-
□	3 P.L.C.	±	-
□	4 P.L.C.	±	-

Customer Print

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Michael Kepko	-	-	
APVD	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex			
SCALE	NTS	SIZE	A2	DRAWING NO
				C- 6278878
SHEET	3 of 3	REV	B1	