

PRODUCT DATASHEET

LED Project Light
Energizer
INDUSTRIAL

INL2DE

DEPENDABLE

- Lasts 32 hours between battery changes
- Lifetime pushbutton switch



RUGGED

- Survives a 1-meter drop
- Chemical resistant polypropylene body
- Virtually unbreakable LEDs
- Shatterproof lens



BRIGHT

- Four white Nichia® LEDs provide 35 lumens of light
- Uniform beam profile



WATERPROOF

- Meets IECEx IPX7 requirements
- Submerge in 1 meter of water for 30 minutes



Rugged and dependable, the Energizer® Industrial® LED Project Light is a great addition to any toolbox. Count on it wherever you need bright, consistent light – even in wet conditions. It features a textured non-slip grip and is waterproof. In addition, the batteries will last for 32 hours of continuous use before you need to replace them, keeping your cost of ownership low. The Energizer® Industrial® LED Project Light is an excellent on-the-job lighting choice.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation: Energizer Industrial LED Project Light

Model: INL2DE

Color: Yellow and Black

Power Source: Two "D"

ANSI / NEDA: Series 13

Lamp: 4 White LEDs

Lamp Life (hr): Lifetime

Lamp Output (lumens): 35

Beam Distance (m): 35

Peak Beam Intensity (cd): 306

Run Time (h:mm): 32


Typical Weight: 168.3 grams
without batteries

Dimensions (mm): 65 x 205

Performance:

Run Time

Continuous Drain to
End of Useable Light (21° C)



Tested according to ANSI / NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty

©Energizer / All Rights Reserved