







Loading-Plan

A — blue — B
B — orange — A



For Information Only
won't be replaced when changed

-Protection level: IP67/65
-Temperature range: -40°C ...+70°C

9	High strength fiber optic breakout cable multimode	33 58 211 300 0001	300 m
8	High strength fiber optic breakout cable multimode	33 58 211 100 0001	100 m
7	High strength fiber optic breakout cable multimode	33 58 211 060 0001	60 m
6	High strength fiber optic breakout cable multimode	33 58 211 050 0001	50 m
5	High strength fiber optic breakout cable multimode	33 58 211 040 0001	40 m
4	High strength fiber optic breakout cable multimode	33 58 211 020 0001	20 m
3	High strength fiber optic breakout cable multimode	33 58 211 010 0001	10 m
2	High strength fiber optic breakout cable multimode	33 58 211 005 0001	5 m
1	High strength fiber optic breakout cable multimode	33 58 211 001 0001	1 m
Cont No.	Type of cable	Part-No.	Dim. a

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances			
				Dat.	Name	Maßstab/Scale 2:1	Push Pull fiber optic assembly 2xPush Pull LC DUPLEX, plastic multimode, 62.5 µm		
			Detail.	16.04.08	MS				
35601	17.02.09	MR	Insp.						
35025	10.11.08	MS	Stand.						
35007	04.08.08	MS	HARTING Electronics GmbH & Co. KG				TB 33 58 211 xxx 0001		Blatt/ page /
34546			D-32339 ESPELKAMP						
Mod.	Dat.	Name				Sub.		Sub	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33582110010001](#) [33582110050001](#) [33582110100001](#) [33582110200001](#) [33582110400001](#) [33582110500001](#)
[33582111000001](#)