

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
GP	00		J	REVISED PER ECO-12-021696	28FEB2013	CJV
						CWR

D

C

B


A

D

C


B

A



- 1 PHOSPHOR BRONZE PER QQ-B-750.
- 2 GOLD PLATED AREA AS FOLLOWS: PLATED WITH 0.76μm [.000030] GOLD IN LOCALIZED GOLD PLATE AREA, .000100 MIN MATTE TIN IN ZONE 1, OVER 1.27μm [.000050] MIN NICKEL. OR GOLD FLASH OVER PALLADIUM-NICKEL PLATE, 0.76μm [.000030] MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000100 MIN MATTE TIN IN ZONE 1, OVER 1.27μm [.000050] MIN NICKEL.
- 3 GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290.
- 4 WILL ACCEPT 1.02 [.040] DIA PIN.
5. 1.17 [.046] MAX DIA CONDUCTOR (UP TO 18 AWG).

SMALL PACK	LOOSE PIECE	1-66569-0
STANDARD	LOOSE PIECE	66569-3
-	STRIP	66569-2
PACKAGING	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN D.HARDY 08 NOV 95	 TE Connectivity				
		CHK R.STONE 14 NOV 95					
DIMENSIONS: mm [INCHES]		APVD C.STINSON 06 DEC 95	NAME SOCKET CONTACT, SIZE 20 DF, WITH SOLDER CUP, AMPLIMITE				
		PRODUCT SPEC —					
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT —	A2	00779	C-66569	—	
		CUSTOMER DRAWING		SCALE	10:1	SHEET 1 of 1	REV J