





AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

- 1 STAMP 5S AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
2. WIRE INSUL DIA, 2.67-3.56 [0.105-0.140]
3. TONGUE MATL THK, 0.79±0.05 [0.031±0.002]
- 4 MATERIAL: BODY - BRASS PER ASTM B36
SLEEVE - PVC, COLOR - RED

100	LOOSE PIECE, BOX	8-52948-1
5000	ON TAPE, REEL	52948-1
1000	LOOSE PIECE	52948
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L OLMEDA 26JUN95		 Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608															
DIMENSIONS: mm[INCHES]			CHK M ELLIS 26JUN95																	
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, SPRING SPADE, SHORT, PLASTI-GRIP, WIRE SIZE: 22-16															
			0 PLC ± -					APVD G NGO 26JUN95												
			1 PLC ± -					PRODUCT SPEC												
			2 PLC ± 0.20 [.008]					UL 486A												
			3 PLC ± -		SIZE A3			CAGE CODE 00779			DRAWING NO C-52948			RESTRICTED TO —						
			4 PLC ± -																	
			ANGLES ± -		APPLICATION SPEC —															
MATERIAL			FINISH		WEIGHT		—													
— 4			TIN PER ASTM B545		CUSTOMER DRAWING															
					SCALE			6:1			SHEET			1 OF 1			REV		K	