

FEATURES

- Body and frame in strong pressure die-cast LM6M high corrosion resistance aluminium. Textured black full polyester powder finish
- Fixings outside gasket line to preserve IP rating
- Covers in prismatic polycarbonate or 9mm thick (nominal) thermally shock resistant borosilicate glass
- Clip-on nylon coated steel wire guard available
- Tamper-resistant cover screws available
- Aluminium gear tray with LED bar
- 60,000 hour LED life expectancy
- Fitted with 4000K LEDs


IP65 

LED CHARACTERISTICS

Ra	°K	L70/B10	P/U	%	R/Rx	PF	LL/W
70	4000	60K	P	>85	R	>0.95	79.9


PHOTOMETRIC GUIDE

POLYCARBONATE



Luminaire Lumen Output:
20W - 1600 lm
32W - 2610 lm

GLASS



Luminaire Lumen Output:
20W - 1720 lm
32W - 2770 lm



RANGE

LED	CAT. No.	APPROX. kg
Polycarbonate Cover		
20W	PX 14932L	4.0
32W	PX 14934L	4.0
Glass Cover		
20W	PX 14933L	6.2
32W	PX 14935L	6.2
Retro-fit Gear Tray		
20W	PX 14936L	1.6
32W	PX 14937L	1.6

ACCESSORIES

DESCRIPTION	CAT. No.
Steel wire guard (black nylon coated)	WG 5071
Tamper-resistant screw kit	SCR 6758
Key for tamper-resistant screw kit	KY 6759



Retro-fit Gear Tray

DIMENSIONS

