



LOC		DIST				REVISIONS					
G		86		P	F	ZONE	LTR	DESCRIPTION		DATE	APPD
							E	REV PER 0G3A-0561-01		030CT02	JR/MS



1 STAMP AMP 1/0C 100 275/24 APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [0.008] 3 PLC DEC ± - ANGLES ± -		DR 30AUG94 DK SCHRUM		53680-2		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER PER ASTM B-75 ANNEALED		CHK 31AUG94 AJ KAUFMAN		PART NO		
FOR APPLICATION TOOLING INFORMATION			CIRCULAR MIL AREA: 42.41-60.55mm ² [83,700-119,500] CIR MILS STRANDED		FINISH TIN PLATE 0.00381 [0.00150] MIN THK PER MIL-T-10727		APPD 31AUG94 RE ROSER		NAME TERMINAL, AMPOWER, WIRE SIZE: 1/0 AWG		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				APPD 31AUG94 JL MECKLEY		SIZE C 00779 C=53680		
							PRODUCT SPEC -		CAGE CODE 00779		
							APPLICATION SPEC -		DRAWING NO C=53680		
							WEIGHT -		SCALE 2:1		
									SHEET 1 OF 1		