



Color :  White

UPC Code : 078477495179

Country Of Origin : Mexico

Available Colors :



Brown



Gray



Ivory



Red

M1221-WL

20 Amp, 120/277 Volt, Single-Pole AC Tamper-Resistant Key Toggle Switch, Extra Heavy Duty Specification Grade, Self Grounding, Lev-Lok Modular – WHITE
Mating Lev-Lok Wiring Module Required for Use

Technical Information

AC Horsepower Ratings

HP Rating : 1HP-120V 2HP-240V

Electrical Specifications

Amperage : 20 A

Dielectric Voltage : Withstands 1500V for 1 minute

Endurance : 50,000 cycles minimum

Grounding : Self-Grounding

Overload UL20 Test : 100 cycles of OL at 4.8 times rated current

Temperature Rise : Maximum 30 degrees C rise

Voltage : 120/277 VAC

Environmental Specifications

Flammability : Rated V-2 per UL94

Operating Temperature : -40°C to 65°C

Material Specifications

Base Material : PBT

Color : White

Contact Material : Silver Alloy

Cover Material : Nylon

Dome : Nylon

Ground Clips : Brass

Strap Material : Galvanized Steel

Toggle : Polycarbonate

Mechanical Specifications

Product ID : Markings are permanently marked on device

Termination : Modular

Product Features

Brand : Lev-Lok

Color : White

Device Type : Tamper-Resistant Toggle Switch

Function : Single-Pole

Grade : Extra Heavy-Duty Industrial Specification Grade

Standards and Certifications

ANSI : C-73

NEMA : WD-1 & WD-6

NOM : 057

RoHS : Compliant

Warranty : 10-Year Limited

cULus : File # E7458

Patents*

CA2655707

US7666010

CA2667092

US8096818

US7357652

*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

