






LOC	DIST	REVISIONS					
ES	18	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AE3	REVISED PERECO-13-006318	13MAY13	RW	SY



	3-88637-8	2,5,10,16,	18,25,30,34	2.210	2.460	1.950	1.834	1.880	34		3-88637-7
	3-88637-6	2,5,10,15,20,25,30,34	36,40,45,50,55,60,65,70	4.010	4.260	3.750	3.634	3.680	70		3-88637-5
	3-88637-4	2,5,10,15,20,25,32,	34,40,45,50,55,60,66	3.810	4.060	3.550	3.434	3.480	66		3-88637-3
	3-88637-2	2,5,10,15,20,25,29,	31,35,40,45,50,55,60	3.510	3.760	3.250	3.134	3.180	60		3-88637-1
	3-88637-0	2,5,10,15,20,25,28	30,35,40,45,50,55,58	3.410	3.660	3.150	3.034	3.080	58		2-88637-9
	2-88637-8	2,5,10,15,20,24	26,30,35,40,45,50	3.010	3.260	2.750	2.634	2.680	50		2-88637-7
	2-88637-6	2,5,10,15,21,	23,30,35,40,44	2.710	2.960	2.450	2.334	2.380	44		2-88637-5
	2-88637-4	2,5,10,15,19,	21,25,30,35,40	2.510	2.760	2.250	2.134	2.180	40		2-88637-3
	2-88637-2	2,5,10,15,18,	20,25,30,35,38	2.410	2.660	2.150	2.034	2.080	38		2-88637-1
	2-88637-0	2,5,10,17,	19,25,30,36	2.310	2.560	2.050	1.934	1.980	36		1-88637-9
	1-88637-8	2,5,10,13,	15,20,25,28	1.910	2.160	1.650	1.534	1.580	28		1-88637-7
	1-88637-6	2,5,12	14,20,26	1.810	2.060	1.550	1.434	1.480	26		1-88637-5
	1-88637-4	2,5,11,	13,20,24	1.710	1.960	1.450	1.334	1.380	24		1-88637-3
	1-88637-2	2,5,9,	11,15,20	1.510	1.760	1.250	1.134	1.180	20		1-88637-1
	1-88637-0	2,5,8,	10,15,18	1.410	1.660	1.150	1.034	1.080	18		88637-9
	88637-8	2,4	8,10	1.010	1.260	.750	.634	.680	10		-88637-7
	88637-6	2	4,6	.810	1.060	.550	.434	.480	6		88637-5
	88637-4	2,5,7,	9,16	1.310	1.560	1.050	.934	.980	16		88637-3
	88637-2	2,5	7,10,12	1.110	1.360	.850	.734	.780	12		88637-1
LASER MARKED PART NO	NEAR SIDE	FAR SIDE		E	D	C	B	A	NO. OF POSN	AS MOLDED	
 	CAVITY POSN. NO. STAMPED 									PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN KATE HELM	11/02/88	 TE Connectivity	
		CHK D. L. ROCKER	2-24-89		
DIMENSIONS: INCHES 					