


3mm Prism® CBI® Circuit Board Indicator Surface Mount LED, Round Lens

Dialight

591-3x0x-0xx

1



Part Number* Type

591-3001-0xx Super Red/Green Bi-Color

591-3101-0xx Yellow/Green Bi-Color

591-3201-0xx Super Red/Yellow Bi-Color

591-3503-0xx Red/Blue/Green Tri-Color

NEW

Features

- Helps to eliminate mixed technology PC board processing.
- Unique patented low part count design.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase solder processes.
- Packaged on 16mm tape, 7" or 13" reels per EIA-481-2.
- Black housing enhances contrast ratio.
- Housing material meets UL94V-0 flammability rating.
- Lens material meets UL94-HB flammability rating.
- Uses LEDs designed specifically for surface mounting.

U.S. Patent RE 34,254; foreign patents pending.

*ORDERING INFORMATION

591-3x01-0xx

packaging option

02	20 pieces on tape
07	7" reel, 400 pcs/reel
13	13" reel, 1600 pcs/reel

NEW

Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$)

Parameter	-3001	-3101	-3201	-3503
Color*	30	31	32	35
Power Dissipation	100mW	100mW	100mW	150mW Total
Forward DC Current	30mA	30mA	30mA	20mA single chip on 30mA all chips on
Peak Forward Current (10μsec)	500mA	500mA	500mA	
Operating Temperature	-55°C to +100°C			
Storage Temperature	-55°C to +100°C			
Soldering Temperatures	235° Peak, above 185° for 90 sec., 215°C for 3 Min.			
Convection IR				
Vapor Phase				

Solder Adherence per MIL-STD-202E, Method 208C

* LED colors: 30) Super Red/Green Bi-Color 31) Yellow/Green Bi-Color 32) Super Red/Yellow Bi-Color 35) Red/Blue/Green Tri-Color

Operating Characteristics ($T_A = 25^{\circ}\text{C}$)

Parameter	Part No.	Color	Min	Typ	Max	Units	Test Cond.
Forward Voltage V_F	-3001	30		2/2	2.6/2.6	V	$I_F=10\text{ mA}$
	-3101	31		2/2	2.6/2.6		
	-3201	32		2/2	2.6/2.6		
	-3503	35		2/3.8/2	2.6/4.5/2.6		
Reverse Voltage V_R	-3001	30	5/5			V	$I_R = 10\text{ }\mu\text{A}$
	-3101	31	5/5				
	-3201	32	5/5				
	-3503	35	5/1/5				
Dominant Wavelength λ_{Dom}	-3001	30		628/570		nm	
	-3101	31		586/570			
	-3201	32		628/586			
	-3503	35		645/466/570			
Luminous Intensity I_V	-3001	30		6.5/8		mcd	$I_F = 20\text{ mA}$
	-3101	31		6.5/8			
	-3201	32		6.5/6.5			
	-3503	35		10/5/16			
Viewing Angle ($2\Theta_{1/2}$)	-3001	30		40/40		deg.	
	-3101	31		40/40			
	-3201	32		40/40			
	-3503	35		40/40/40			

$\Theta_{1/2}$ is the off axis angle at which the luminous intensity is half the axial luminous intensity

* LED colors: 30) Super Red/Green Bi-Color 31) Yellow/Green Bi-Color 32) Super Red/Yellow Bi-Color 35) Red/Blue/Green Tri-Color

