












COPALUM TERMINALS AND SPLICES		WIRE SIZE (AWG Unless Indicated Otherwise)			HYDRAULIC TOOLING For Power Units 69120, 314979-1, or 122271-1				PNEUMATIC TOOLING			HEAVY HEAD HAND TOOL	TOOLING AND ACCESSORIES				
		TERMINAL OR PARALLEL SPLICE	BUTT SPLICE		DIES for Head				DIES for Head		JAWS For Head 68068		Hydraulic				
			Aluminum (AL)	Copper (CU)	69066	69082	69099	58422-1	626	69015			DYNA-CRIMP* Hydraulic Power Units 69120-1 (115 VAC, 60 Hz) 69120-2 (230 VAC, 60 Hz)		Hand-Operated Hydraulic Pump 314979-1		
Bar Crimp For Solid or Stranded Aluminum or Copper Wire 	20-18	20-18	22-20								68040						
	16-14	16-14	20-18								68041						
	12-10	12-10	16-14							68105	68042						
	8	8	12-10			68043			68032	68105							
	6	6	8			68044			69999	68106							
	4	4	6			68045			68038								
	2	2	4			68046											
	1/0	1/0	2			68047											
	2/0	2/0	1/0			68048											
	3/0	3/0	2/0			68049											
	4/0	4/0	3/0		68050												
	250 MCM	250 MCM	4/0		68034												
	300 MCM	300 MCM	250 MCM		68035												
	400 MCM	400 MCM	300 MCM		68036												
	500 MCM	500 MCM	400 MCM		68037												
Insulation Piercing Crimp For Film-Insulated Solid Aluminum and Copper Wire or Stranded Copper Wire 	16-14	16-14	18-16					189447-1		68100	68140-1						
	12-10	12-10	14-12					189444-1		68100 68101	68141-1						
	8	8	12-10			68084				68101 68192-1							
	6	6	8			68085			68082	68102							
	4	4	6			68086											
	2	2	4			68130											
	1/0	1/0	2			68131											
	2/0	2/0	1/0			68132											
	3/0	3/0	2/0			68133											
	4/0	4/0	3/0		68129	318106-1											
	8	8	10	68006			68006							Pneumatic			Manual
	6	6	8-6	68007			68007										
	4	4	8-6	68008			68008										
			4														
	2	2	4	68009			68009										
1/0	1/0	2	68010			68010											
		4															
2/0	2/0	1/0	314964-1			68011-1											
3/0	3/0	2/0				59877-1											
4/0		1/0				314948-1											