

**521 SERIES INCANDESCENT LAMPS****T-3 1/4 MINIATURE BAYONET BASE**

| PART NO. | LAMP NO. | VOLTS  | AMPS | MSCD | LIFE HOURS |
|----------|----------|--------|------|------|------------|
| –        | 49       | 2.0    | .06  | 0.04 | 1,000      |
| –        | 45       | 3.2    | .35  | 0.50 | 3,000      |
| –        | 47       | 6.3*   | .15  | 0.50 | 3,000      |
| –        | 1847     | 6.3*   | .15  | 0.38 | 3,000      |
| –        | 44       | 6.3*   | .25  | 0.90 | 3,000      |
| –        | 1866     | 6.3*   | .25  | 0.65 | 20,000     |
| 521-0755 | 755      | 6.3*   | .15  | 0.33 | 20,000     |
| –        | 1891     | 14.0*  | .24  | 2.0  | 500        |
| 521-1815 | 1815     | 14.0*  | .20  | 1.4  | 3,000      |
| 521-0756 | 756      | 14.0*  | .08  | 0.31 | 15,000     |
| –        | 1819     | 28.0*  | .04  | 0.34 | 2,500      |
| –        | 1829     | 28.0*  | .07  | 1.0  | 1,000      |
| –        | 1820     | 28.0*  | .10  | 1.6  | 1,000      |
| 521-0313 | 313      | 28.0*  | .17  | 3.5  | 500        |
| 521-0757 | 757      | 28.0*  | .08  | 0.62 | 7,500      |
| –        | 1828     | 37.5   | .05  | 0.65 | 3,000      |
| 521-1835 | 1835     | 55.0   | .05  | 1.1  | 5,000      |
| 521-9109 | 120MB    | 120.0* | .025 | 0.36 | 10,000     |



T-3 1/4 MINIATURE  
BAYONET BASE  
INCANDESCENT LAMP

\* Also available in T-3 1/4 multichip and T 3 1/4 cluster Based LED versions. See pages 39 and 40 for information.

Note: 120 volt version only available in T-3 1/4 cluster version. See page 40 for information.

**S-6 DOUBLE CONTACT BAYONET BASE**

| PART NO. | LAMP NO.    | VOLTS | AMPS  | LIFE HOURS |
|----------|-------------|-------|-------|------------|
| –        | 6S6DC-24V   | 24    | 0.025 | 3,000      |
| –        | 6S6DC-30V   | 30    | 0.2   | 3,500      |
| –        | 6S6DC-48V   | 48    | 0.125 | 3,500      |
| 521-9080 | 6S6DC-75V   | 75    | 0.08  | 3,000      |
| 521-9081 | 6S6DC-125V  | 125   | 0.05  | 4,000      |
| –        | 6S6DC-135V  | 135   | 0.05  | 3,000      |
| –        | 6S6DC-145V  | 145   | 0.04  | 3,800      |
| –        | 10S6DC-230V | 230   | 0.04  | 3,000      |
| 521-9096 | 10S6DC-250V | 250   | 0.04  | 3,000      |



S-6 DOUBLE CONTACT  
BAYONET BASE  
INCANDESCENT LAMP

**S-6 CANDELABRA SCREW BASE**

| PART NO. | LAMP NO.  | VOLTS | AMPS  | LIFE HOURS |
|----------|-----------|-------|-------|------------|
| 521-9062 | 6S6-6V    | 6     | 1.0   | 3,000      |
| 521-9063 | 6S6-12V   | 12    | 0.5   | 3,000      |
| 521-9064 | 6S6-24V   | 24    | 0.25  | 3,000      |
| –        | 6S6-30V   | 30    | 0.2   | 3,500      |
| –        | 6S6-48V   | 48    | 0.125 | 3,500      |
| –        | 6S6-75V   | 75    | 0.08  | 3,000      |
| 521-9068 | 6S6-125V  | 125   | 0.05  | 4,000      |
| 521-9072 | 6S6-135V  | 135   | 0.05  | 3,000      |
| –        | 6S6-145V  | 145   | 0.04  | 3,800      |
| –        | 10S6-230V | 230   | 0.04  | 3,000      |



S-6  
CANDELABRA  
SCREW BASE  
INCANDESCENT LAMP

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[521-1815](#) [521-0313](#) [521-9081](#) [521-9109](#) [521-9064](#) [521-9068](#) [521-9063](#) [521-0756](#) [521-0755](#) [521-0757](#)