



- Durable nylon cable clamps

Part Number:	CCS38-S8-C
Product Family:	Fixed Diameter Cable Clamps
Product Line:	Screw/Rivet Applied
RoHS Compliancy Status:	Compliant
Part Description:	Fixed Diameter Cable Clamp
Product Type:	Mounting Device
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Diameter (In.):	.17
Diameter (mm):	4.2
Width (In.):	.37
Width (mm):	9.4

Bundle Offset (mm):	15.0
Bundle Offset (In.):	.59
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.17
Hole Diameter (mm):	4.2
Max. Bundle Diameter (In.):	.38
Max. Bundle Diameter (mm):	9.5
Metric Screw Size:	M4
Mounting Method:	#8 (M4) Screw
Screw Size:	#8 (M4)
Std. Pkg. UOM:	PK
Type Of Application:	Standard
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100