



**Wiha Quality Tools**  
Germany

Go To  
Image Index

Go To  
Numerical Index

20

Toll Free: (800) 494-6104

## Wiha TORX® MicroFinish Handle Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

Safe, high density material,  
eliminates risk of sharp objects  
becoming embedded in the handle

Blades are hardened  
& hard chromed

Exact  
fit precision  
ground tips



MicroFinish Handle with patented  
non-slip surface. Ergo handle  
shape for maximum comfort &  
exceptional torque transfer

Blade CVM, hardened & tempered tool  
steel, gives exceptional tool life, wear  
resistance & high torque performance



### 527 TORX® Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 527 11   | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .15  | 10   |
| 527 13   | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .15  | 10   |
| 527 16   | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .15  | 10   |
| 527 19   | T20  | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .15  | 10   |
| 527 22   | T25  | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .16  | 10   |
| 527 26   | T27  | 115 | 4.5  | 5.5 | .216 | 233 | 9.2  | .25  | 10   |
| 527 29   | T30  | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .27  | 10   |
| 527 32   | T40  | 130 | 5.1  | 7.0 | .275 | 254 | 10.0 | .40  | 10   |



**See MicroFinish Non-Slip Grip  
Screwdrivers On Page 73-74**



### 527 90 Set 5 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

| Item   |        |  |     |  |  |  |     |  |  |  |     |
|--------|--------|--------------------------------------------------------------------------------------|-----|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-----|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-----|
| No.    |        | Size                                                                                 | mm  |                                                                                       |  | Size                                                                                  | mm  |                                                                                       |  | lbs.                                                                                  |     |
| 527 90 | 527 13 | T10                                                                                  | 80  |                                                                                       |  | 527 22                                                                                | T25 | 100                                                                                   |  |                                                                                       | 1.0 |
|        | 527 16 | T15                                                                                  | 80  |                                                                                       |  | 527 29                                                                                | T30 | 115                                                                                   |  |                                                                                       |     |
|        | 527 19 | T20                                                                                  | 100 |                                                                                       |  |                                                                                       |     |                                                                                       |  |                                                                                       |     |



### 527 91 Set 8 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Resistant, non-slip, oil and grease resistant.

| Item   |  |  |     |  |  |     |  |
|--------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----|---------------------------------------------------------------------------------------|
| No.    | Size                                                                                 | mm                                                                                    |     | Size                                                                                  | mm                                                                                    |     | lbs.                                                                                  |
| 527 91 | 527 11                                                                               | T9                                                                                    | 60  | 527 22                                                                                | T25                                                                                   | 100 | 1.89                                                                                  |
|        | 527 13                                                                               | T10                                                                                   | 80  | 527 26                                                                                | T27                                                                                   | 115 |                                                                                       |
|        | 527 16                                                                               | T15                                                                                   | 80  | 527 29                                                                                | T30                                                                                   | 115 |                                                                                       |
|        | 527 19                                                                               | T20                                                                                   | 100 | 527 32                                                                                | T40                                                                                   | 130 |                                                                                       |

PREVIOUS

NEXT