




PRODUCT RANGE (RATINGS @ 85°C)				
TYPE	CONTINUOUS		TRANSIENT	
	RMS VOLTAGE (VOLTS)	DC VOLTAGE (VOLTS)	ENERGY (10/1000ms) (JOULES)	PEAK CURRENT (8/20ms) (AMPS)
DVS 24	30	38	8.8	1000
DVS 48	60	81	20	4500
DVS 110	150	200	80	6500
DVS 240	275	369	140	6500

SPECIFICATION




LINE FREQUENCY DC TO 440HZ

TEMPERATURE RANGE -25C TO +85C

WIRE GUAGE 12 AWG

MOUNTING EN 50 022 RAIL (TOP HAT)

SCREW TERMINALS 2.5sq.mm (12 AWG)



ALL DIMENSIONS IN MM / ANGLES IN DECIMAL DEGREES

DrgNo DVS-GS

TITLE DIMENSIONS FOR DVS24,48,110,240



ISSUE

1

GENERAL SPECIFICATION
FOR DVS

CUSTOMER
FILTER REF

Sheet 1 of 1 | Aprvd Date 19/03/01 | Aprvd By SW | Drwn by BFS | SCALE NTS | CNN--- | Location N:\DWG\GS\GS000236

©DELTRON EMCON LTD, ROXBURGH HOUSE, FOXHILLS INDUSTRIAL PARK, SCUNTHORPE, NORTH LINCOLNSHIRE, DN15 8QJ TEL +44 1724 281770 F +44 1724 270230