


Werkstattmeßschieber

mit Messerspitzen, ohne Feineinstellung

Ausführung:

DIN 862
Feststellschraube
Lochmaßansatz:
0-300 mm = 10 mm
400-1000 mm = 20 mm
rostfreier Stahl
Nonius + Skala mattverchromt
einschließlich Etui



Vernier calipers

with knife-edge, without fine adjustment

Techn. data:

DIN 862
Locking screw
Measuring jaws:
0-300 mm = 10 mm
400-1000 mm = 20 mm
stainless steel
scale and vernier satin chromed
individually packed

Pieds à coulisse d'atelier

avec becs extérieurs fins, sans réglage fin

Applications:

DIN 862
vis de blocage
extrémités des becs pour mesures:
0-300 mm = 10 mm
400-1000 mm = 20 mm
vernier et échelle chromés mats
en inox
emballés à l'unité


> mm <	 mm	 inch	 mm	No.	€	
250	0,05	1/128	80	111-21		
300	0,05	1/128	100	111-22		
400	0,05	1/128	125	111-33		
500	0,05	1/128	150	111-34		
600	0,05	1/128	150	111-35		
800	0,05	1/128	150	111-36		
1000	0,05	1/128	150	111-37		

Werkstattmessschieber

mit Messerspitzen, mit Feineinstellung

Ausführung:

DIN 862
Feststellschraube
Lochmaßansatz:
0-300 mm = 10 mm
400-1000 mm = 20 mm
rostfreier Stahl
Nonius + Skala mattverchromt
einschließlich Etui



Vernier caliper

with knife-edge, with fine adjustment

Techn. data:

DIN 862
Locking screw
Measuring jaws:
0-300 mm = 10 mm
400-1000 mm = 20 mm
stainless steel
scale and vernier satin chromed
individually packed

Pieds à coulisse d'atelier

avec becs extérieur, avec réglage fin

Applications:

DIN 862
vis de blocage
extrémités des becs pour mesures:
0-300 mm = 10 mm
400-1000 mm = 20 mm
vernier et échelle chromés mats
en inox
emballés à l'unité

> mm <	 mm	 inch	 mm	No.	€	
250	0,05	1/128	80	111-51		
300	0,05	1/128	100	111-52		
400	0,05	1/128	125	111-63		
500	0,05	1/128	150	111-64		
600	0,05	1/128	150	111-65		
800	0,05	1/128	150	111-66		
1000	0,05	1/128	150	111-67		

> mm <



Messbereich
Ablesung mm / inch
Schnabellänge

Range
Reading mm / inch
Length of jaws

Capacité
Lecture mm / inch
Longueur des becs