

Datasheet

Item No. 80.010.0010.0

Relay module WRS-REL-1W-250V16

WRS-relays, contact Assignment: 1 change-over contact, input voltage: 20 V AC/DC, output voltage: 250 V AC, switching current max. 16A AC, type: WRS-REL-1W-250V16

Item No.	80.010.0010.0
EAN	4015573357990
order unit	5 Piece(s)

Approvals

Technical data

General

Connection type	Screw connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Nominal voltage DC	24 V
Lower nominal voltage DC	20.4 V
Upper nominal voltage DC	26.4 V

Dimensions

Depth	60 mm
Width	22.5 mm
Height	80 mm

Accessories

Item. No.	Typ:	Description:
-----------	------	--------------

Drawings