




MAT Range of Stainless Steel Cable Ties

Features and Benefits


The MAT ties are similar in design to conventional 'plastic' cable ties and work on a ratchet system. Available in type 316 stainless steel.



Stainless Steel Cable Ties can be used at temperatures up to 538° C.



MAT



Material specification
please see page 83.

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Application Tool
MAT Uncoated							
111-92080	MAT8SS7	230	7.0	60.0	445	SS316	MTT6
111-92120	MAT12SS7	330	7.0	90.0	445	SS316	MTT6
111-92160	MAT16SS7	430	7.0	120	445	SS316	MTT6
111-92240	MAT24SS7	630	7.0	180	445	SS316	MTT6
111-93080	MAT8SS12	230	12.0	60.0	445	SS316	MTT6
111-93120	MAT12SS12	330	12.0	90.0	445	SS316	MTT6
111-93160	MAT16SS12	430	12.0	120	445	SS316	MTT6
111-93240	MAT24SS12	630	12.0	180	445	SS316	MTT6
MAT Fully Coated							
111-92004	MAT8SSC7	230	7.0	60.0	445	SS316, SP	MTT6
111-96120	MAT12SSC7	330	7.0	90.0	445	SS316, SP	MTT6
111-92162	MAT16SSC7	430	7.0	120	445	SS316, SP	MTT6
111-92200	MAT24SSC7	630	7.0	180	445	SS316, SP	MTT6
111-92002	MAT8SSC12	230	12.0	60.0	445	SS316, SP	MTT6
111-92122	MAT12SSC12	330	12.0	90.0	445	SS316, SP	MTT6
111-92163	MAT16SSC12	430	12.0	120	445	SS316, SP	MTT6
111-92201	MAT24SSC12	630	12.0	180	445	SS316, SP	MTT6

All dimensions in mm. Subject to technical changes.