

10072354-X01-XXXLF

PACKAGING (SEE NOTE 5)

S = 0.38 μ m GOLD/GXT
ON CONTACT AREA
2 μ m MIN MATTE
TIN ON TAIL

2μm MIN MATTE
TIN ON TAIL

2μm MIN MATTE TIN ON TAIL

1.2/μm MIN NICKEL UNDERPLATING

NOTES:

- MEETS GWT 850°C 960°C
 - = STANDARD COLOR CREAM
 B = OPTIONAL COLOR BLACK

2. MATERIAL TERMINAL: COPPER ALLOY






3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW

4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.

- = PLASTIC BOX
U = TUBE AVAILABLE FROM 06 TO 50 POS
K = TAPE & REEL WITHOUT PICK UP CAP

6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
- b – MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR
30 SECONDS MAX IN A CONVECTION, INRA-RED
OR VAPOR PHASE OR REFLOW OVEN.
- c – LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d – THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004

[illegible]