

Part Number: **5973303107F**

General Description	
Series	597
Configuration	1210 Package
Description	SMD LED 1210 G 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
LED Type	InGaAlP
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Forward Current mA	25mA
Reverse Current	100 @ Vr =4V
Forward Current Pulsed	100mA
Derating	from 25Â° @ .33mA/Â°C
Operating Temperature	-30~+85
Storage Temperature	-25~+75

Operating Characteristics	
Color	Green
Luminous Intensity Typical	50
Dominant Wavelength Typical	570nm
Power Dissipation Max	100mW



5973303107F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)