



Appliance Oven P45

Appliance 40W E14 240V P45 CL OV 1CT

Lustre vacuum lamps with clear glass (P-bulb)

PHILIPS
sense and simplicity

Product data

• General Characteristics

Cap-Base	SES
Bulb	P45 [P 45mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Main Application	Oven
Nominal Lifetime	1000 hr
Rated Lifetime (hours)	1000 hr
Rated Lifetime (years)	1 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2700 K
Lamp Luminous Flux	420 Lm
Rated Luminous Flux	420 Lm

• Electrical Characteristics

Rated Wattage	40.0 W
Lamp Wattage	40 W
Power Factor	1 -
Voltage	240 V
Lamp Current	0.17 A
Dimmable	yes
Starting Time	0.0 s
Warm-up Time to 60% Light Outp	instant full light

• Environmental Characteristics

Energy Efficiency Label (EEL)	E
-------------------------------	---

Energy consumption kWh/1000h	40 kWh
------------------------------	--------

• Measuring Conditions

Switching cycle	4000X
-----------------	-------


• Product Dimensions

Overall Length C	75 (max) mm
Diameter D	45 mm

• Product Data

Order code	035455 50
Full product code	871150003545550
Full product name	Appliance 40W E14 240V P45 CL OV 1CT
Order product name	Appl 40W E14 240V P45 CL OV 1CT/10X10F
Pieces per pack	1
Packing configuration	10X10F
Packs per outerbox	100
Bar code on pack - EAN1	8711500035455
Bar code on intermediate packing - EAN2	8711500085214
Bar code on outerbox - EAN3	8711500085221
Logistic code(s) - 12NC	923265945546
ILCOS code	IBP/C-40-240-E14-45*
Net weight per piece	15.460 gr


Dimensional drawing



Appliance 40W E14 240V P45 CL OV 1CT

Product	C (Max)	D (Norm)	D (Max)
APP 40W E14 240V P45 CL OV	75	45	-

Dimensional drawing



E14



© 2013 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2013, May 17
data subject to change