



GK17M

General purpose caged air probe



Copyright © 2007 Test Products International, Inc.

Application

Caged exposed junction for fast response in air

Range°F°C

-40° to 586°F
-40° to 308°C

Probe tip

46

Dimensions

Stem Length: 8" (203mm)
Diameter: 0.26" (6.5mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane