


Terminal Blocks



158-P02EK950V2, 158-P02EK950V3

KOBICONN

Terminal Blocks



P.C.B. LAYOUT (REF)



Dimensions: mm and (IN)

P	02P	03P
U	9.52	19.04
V	19.04	28.56

ELECTRICAL SPECIFICATIONS

Rating:	300V 30A
Pitch:	9.52mm
Insulation withstands voltage:	AC 2000V/Min.
Insulation resistance:	500MΩ or more @ 500VDC
Temperature range:	-40°C ~ +105°C
Screw torque value:	5kgf-cm
Electric wire:	26 ~ 10 AWG

MATERIAL SPECIFICATIONS

Solder pin (4):	brass, tin plated
Wire cage (3):	steel, Zn plated
Screw (2):	steel, M3/Zn plated
Housing (1):	PA66

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300254

158-P02EK950V2, 158-P02EK950V3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[158-P02EK950V3](#) [158-P02EK950V2](#)