




FEATURES:

- Ideal for mating to Pomona part number 5547-48-*

MATERIALS:

Pincer:

Finish: Contact - Beryllium Copper, Gold Plated

Insulation: Barrel - Nylon 6, impact modified

Cap - Nylon 6, impact modified

Banana Jack:

Insulation: PVC

Finish: Brass, nickel plated.

Wire: 18 AWG, Silicone

RATINGS:

Operating Temperature: +80°C (176F) Max

Operating Voltage: 300 VRMS/DC

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 5686-10-*

* = Color, -0 Black, -2 Red

Ordering Example: 5686-10-2 Cable Length is 10"(254) Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA