


LOC		DIST		REVISONS			
J		—		変更		DATE	DWN
P		LTR		DESCRIPTION		APVD	
G2				REVISED PER ECR-14-013846		17SEP2014	NK
						DC	



端子挿入時(被覆外形3.1の時)
MATING WITH REC CONTACT
(EX. WIRE INSULATION DIA 3.1)

端子型番
REC CONTACT P/N: 170046-2
電線
WIRE: AWG#14 (2mm²)

- 1 APPLICABLE CONTACT P/N 170046-1, -2, -3, 170096-1, -2, 42640-2, 42731-2, 170095-1, 170213-1, -2, -3, 170183-1, -2, 170187-1, -2, 41450, 41829, 61227-1, 63609-1.
- 2 GENERAL TOLERANCE: ± 0.25 .
- 3 NOT APPLICABLE AWG#10 (5mm²) WIRE CRIMPING CONTACT.
- 4 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1. SECTION 30 (GWT).

UL94 V-0, GWT	NATURAL	7-171706-1
UL94 V-2 調湿品	自然色	2-171706-1
UL94 V-2 MOISTURE ITEM	NATURAL	
タイコエレクトロニクスアンプ韓国製品 Tyco Electronics AMP-KOREA Product	自然色	1-171706-1
UL94 V-0	NATURAL	
UL94 V-2	赤色	171706-2
UL94 V-2	自然色	171706-1
UL94 V-2	NATURAL	
備考	色調	型番
REMARKS	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SATO 04DEC2007	TE Connectivity		
DIMENSIONS: 単位: 特 mm		CHK S. MANABE 04DEC2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S. MANABE 04DEC2007	NAME 名称		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		PRODUCT SPEC 製品規格	250 AMP IP POD		
MATERIAL 材料 66ナイロン 66NYLON		APPLICATION SPEC 取付適用規格	SIZE A3		
FINISH 仕上		WEIGHT	CAGE CODE 00779		
			DRAWING NO C-171706		
			RESTRICTED TO		
			SCALE 尺 NONE		
			SHEET 1 OF 1		
			REV G2		
			CUSTOMER DRAWING		