




- For stranded conductors AWG 28 to AWG 24
- Max wire diameter 1.05mm
- Cat.6A performance class EA suitable for 1/10 Gigabit Ethernet
- Temperature range -40°C up to +70°C
- 750 mating cycles

 		All Dimensions in mm Original Size DIN A4		Scale 2:1		Free size tol.		Ref.					
								Sub.					
		All rights reserved		Created by ATIRIS		Inspected by DAUCHELLE		Standardisation HOFFMANN		Date 2013-03-19		State Final Release	
		Department EC PD - FR										Doc-Key / ECM-Nr. 100520013/UGD/001/B 500000059856	
HARTING Electronics GmbH D-32339 Espelkamp				Title RJ45 Gigalink RJ45 plug Cat6A, 8p									
				Type TB		Number 09451511520						Rev. B	