


TECHNICAL SPECIFICATIONS

Material:	Polyamid UL-recognized
Operating Temperature:	-30°C to 90°C
Cable Entry:	Side and Top Side Only Top Only
Thumbscrews:	UNC 4-40 (standard) M2,5 or M3,0 upon request
Cable Diameter:	Up to 11,5 mm
Colour:	Black
Accessories:	See page 40-43



Features:

- Available in sizes 9-15-25-37
- Suitable for any common D-sub connector
- Quick-snap locking system
- Re-openable
- Company logo available upon request
- Also available in Shielded metalized version
(See MHDSSK-T/M, page 13)

Size DSSK-T/P	Dim A	Dim B	Dim B
9-way	31,5	40,0	43,0*
15-way	40,0	40,0	-
25-way	53,5	43,0	-
37-way	71,3	40,0	-

* Top only

Ordering information:

Hoods in Single-Pack: Side + Top Entry

9-way	6260-0107-01
15-way	6260-0107-02
25-way	6260-0107-03

Side Entry Only:

9-way	6260-0107-11
15-way	6260-0107-12
25-way	6260-0107-13
37-way	6260-0107-14

Top Entry Only:

9-way	6260-0107-21
15-way	6260-0107-22
25-way	6260-0107-23

Hoods in Bulk-Pack: Side + Top Entry

9-way	6261-0107-01
15-way	6261-0107-02
25-way	6261-0107-03

Side Entry Only:

9-way	6261-0107-11
15-way	6261-0107-12
25-way	6261-0107-13
37-way	6261-0107-14

Top Entry Only:

9-way	6261-0107-21
15-way	6261-0107-22
25-way	6261-0107-23