




Bitte wählen Sie die Anzeige-Sprache: [[Englisch](#)] [[Deutsch](#)] [[Beide](#)]

one and two pair AES/EBU & DMX cables

DigiPatch FRNC, extremely flexible



Application:

Highly flexible switching cable for digital signals in accordance with AES/EBU. Due to the small diameter and the very good bending characteristics as switching- or patchcable many-sided applicable.

Construction:

Conductor:	finest, bare stranded copper wire
Structure of conductor:	37x0,07mm
Core insulation:	PE
Shield:	bare copper spiral screen
Jacket:	FRNC (LSZH), black, matt

Technical characteristics:

Capacity:	1 MHz: approx. 67pF/m
Testing voltage:	250V c/c; 1000V c/s
Characteristic impedance:	1 MHz: 110 Ohm +/-10%
Temperature range	static: -15°C to +70°C dynamic: -5°C to +70°C
Bending radius	min. 10 x O.D.

Packaging:

spools at 500 m

**Important product information**

old label: V(W)Hf-H

Product range**DigiPatch FRNC, extremely flexible**

Order no.	dimension (qmm)	O. D. (ca. mm)	weight (kg/km)	co.-weight (kg/km)
99H201400	2x0,14	3,5	19	8,1