


Paper Labels (B-424)

Economical choice for light duty general ID.

- White finish and matte topcoat
- Excellent contrast and smear resistance for bar code printing

Service temp: -40°F to 124°F
Agency approvals: **RoHS**




Fits Printer Model(s)	Diagram	Catalog #	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP33 only	Fig. 2	B33-17-424	White	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-18-424	White	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-19-424	White	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R4300
BBP33 only	Fig. 2	B33-25-424	White	4.000 (101.6)	6.000 (152.4)		6.125 (155.6)	4.200 (106.7)	1	350	B30-R4300

Polypropylene Labels (B-425)

General labeling material for indoor use.

- Outstanding chemical and solvent resistance and print performance
- Not recommended for prolonged outdoor use (use B-595 material on p.14 for 8-10 year outdoor use)

Service temp: -94°F to 212°F
Agency approvals: **UL** **UL** **RoHS** **CE**




Fits Printer Model(s)	Diagram	Catalog #	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP33 only	Fig. 1	B33-5-425	White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R4300
BBP33 only	Fig. 2	B33-17-425	White	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-18-425	White	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-19-425	White	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R4300

Outdoor Grade Vinyl Labels (B-595)

For 8-10 year outdoor use.

- Semi-gloss topcoat
- Good chemical, moisture, UV and weather resistance
- Highly pliable material conforms to rough and curved surfaces and equipment
- Average outdoor durability of the label is 8-10 years, depending on placement

Service temp: -40°F to 180°F
Application temp: 0°F to 180°F



Fits Printer Model(s)	Diagram	Catalog #	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 2	B30-242-595-BLNKWT	White	2.850 (72.4)	1.125 (28.6)		3.250 (82.6)	1.375 (35.0)	1	300	B30-R10000
BBP31, BBP33	Fig. 2	B30-241-595-BLNKWT	White	3.000 (76.2)	2.250 (57.2)		3.250 (82.6)	2.500 (63.5)	1	300	B30-R10000
BBP31, BBP33	Fig. 2	B30-241-595-BLNKYL	Yellow	3.000 (76.2)	2.250 (57.2)		3.250 (82.6)	2.500 (63.5)	1	300	B30-R10000
BBP31, BBP33	Fig. 2	B30-219-595-BLNKWT	White	3.850 (97.8)	2.250 (57.2)		4.250 (108.0)	2.500 (63.5)	1	250	B30-R10000
BBP31, BBP33	Fig. 2	B30-25-595-BLNKWT	White	6.000 (152.4)	4.000 (100.0)		6.250 (158.8)	4.250 (108.0)	1	175	B30-R10000
BBP31, BBP33	Fig. 2	B30-25-595-BLNKYL	Yellow	6.000 (152.4)	4.000 (100.0)		6.250 (158.8)	4.250 (108.0)	1	175	B30-R10000