



HOME

CHECK ORDER

ABOUT US

CONTACT US

REQUEST CATALOG

e-NEWSLETTER

Over 95 Years of Innovation

PRODUCT FAMILIES

Pin Headers
and Sockets

Clips and Insulators

Banana Plugs and Jacks

Grabbers, Probes and
Spade TerminalsTest Leads and Patch
Cords

Plunger Test Leads

Banana Plug Test Leads

Alligator Clip Patch Cords

Coaxial Cable Assemblies

DMM Kits

Stackable Single Banana Plugs on Both Ends



Model # BU-2020-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: hands free testing at 300V, 10 Amps

CHECK INVENTORY

Insulated Alligator Clip to Stackable Banana Plug

SEARCH TOOLS

TOOL
MUELLER OR DISTRIBUTOR
STOCK SEARCH

PART

SEARCH

TOOL
CROSS COMPETITOR PART #

Choose a Brand

PART

SEARCH

TOOL
MeterMate® DMM ACCESSORY
SELECTOR

Select Meter Make

Select a Make First

TOOL
BUILD A PCB HEADER OR
SOCKET
OVER 10,000 IN STOCK! GO

ISO 9001:2000



Model # BU-2030-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Alligator Clip: nickelplated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: hands free testing at 300V, 10 Amps

CHECK INVENTORY

Insulated Mini-Alligator Clip to Stackable Banana Plug



Model # BU-2031-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Alligator Clip: nickelplated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red

- Rating: hands free testing at 300V, 10 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Right Angle Shrouded Banana Plug



Model # BU-2241-D-48-*

- Material: Needle: stainless steel; Banana plugs: nickel-plated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000V Category II, 20 Amps

CHECK INVENTORY

Shrouded Right Angle Banana Plug



Model # BU-2243-D-48-*

- The stainless steel probe is Teflon® insulated except for the working end to prevent unwanted contact with other components that may be in the way
- Material: Needle: stainless steel; Banana Plugs: nickel-plated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 20 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Unshrouded Banana Plug



Model # BU-2641-D-48-*

- Material: Needle: stainless steel; Banana Plugs: nickel-plated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 10 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Unshrouded Banana Plug



Model # BU-2741-D-48-*

- Material: Needle: stainless steel; Banana plugs: nickel-plated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 10 Amps

CHECK INVENTORY

CHECK INVENTORY

Unshrouded Banana Plugs on Both Ends °C Ultra-Flex-Silicone



Model # BU-2929-M-**-*

- Material: Unshrouded Banana Plugs: Mueller No. Bu-16-*; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- **Length: -10" (.25m), 20" (.5m), 39" (1m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 3 kV, 20 Amps

CHECK INVENTORY

Shrouded Banana Plug to Safety Test Prod °C Silicone



Model # BU-4061-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Probe: stainless steel tip with 8-32 UNC thread. Hook up wire: #18 AWG, silicone insulator.
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue.
- Rating: 1000V, 20 Amps, IEC 1010 compliant

CHECK INVENTORY

Shrouded Right Angle Banana Plug to Safety Test Prod - Silicone



Model # BU-4062-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Probe: stainless steel tip with 8-32 UNC thread. Hook up wire: #18 AWG, silicone insulator.
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue.
- Rating: 1000V, 20 Amps, IEC 1010 compliant

CHECK INVENTORY

Stackable 0.080" (2.0mm) Pin Plug on Both Ends



Model # BU-4444-A-**-*

- Tip jack accepts 0.080" (2.0mm) diameter pin jack contact
- Material: Pin Plug: 0.080" (2.0mm) diameter; 0.500" (12.7mm) long, nickel-plated brass pin tip, nickel-plated beryllium copper spring, ABS housing. Hook-up Wire: #22 (19/34) AWG tinned copper with 105°C PVC insulation
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300VAC, 15 Amps

CHECK INVENTORY

Shrouded Banana Plug on Both Ends "C Silicone



Model # BU-6161-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Hook up wire: #18 AWG, silicone insulator
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 20 Amps, IEC 1010 Compliant

CHECK INVENTORY

Right Angle Shrouded Banana Plug to Shrouded Banana Plug "C Silicone



Model # BU-6162-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring; Hook up wire: #18 AWG, silicone insulator
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 20 Amps, IEC 1010 Compliant

CHECK INVENTORY

Stackable Dual Banana Plug to Mini-Micro-Plunger with RG58



Model # BU-7014-B-**-*

- Material: Plunger: nylon housing, stainless steel spring and beryllium copper contact. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

CHECK INVENTORY

Stackable Dual Banana Plug to Stackable Single Banana Plug with RG58



Model # BU-7020-B-**-*

- Material: Single Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)

- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 500 VRMS

CHECK INVENTORY

Stackable Dual Banana Plug to Mini-Alligator Clip with RG58



Model # BU-7031-B-**-*

- Material: Alligator clip: nickel-plated steel with PVC insulator. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

CHECK INVENTORY

Stackable Dual Banana Plug to Stackable Pin Plug with RG58



Model # BU-7044-B-**-*

- Material: Pin Plug: 0.080" (2.0mm) diameter; 0.500" (12.7mm) long, nickel-plated brass pin tip, nickel-plated beryllium copper spring, ABS housing. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 500 VRMS

CHECK INVENTORY

Stackable Double Banana Plug on Both Ends with RG58



Model # BU-7070-B-**-*

- Material: Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf

cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.

- Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

CHECK INVENTORY

Shrouded Double Banana Plug on Both Ends with RG58



Model # BU-7171-B-**-0

- Material: Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded #22 AWG (7/30) twisted pair with drain connected to (-) side of one banana plug; side with drain connection is marked. Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 500 VRMS

CHECK INVENTORY

0.025in(0.6mm) Square Pin Receptacle - Both Ends



BU-8080-E-**-*

Model

- Material: Pin Receptacle: ABS housing, 0.025" (0.6mm) copper-nickel-tin alloy 725 with 0.000030" (0.00076mm) gold contact plating conductor. Hook-up Wire: #22 AWG (19/34) tinned copper with 105°C PVC insulation.
- Length: -6" (.15m), 12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300V, 3 Amp

CHECK INVENTORY

© 2005 Mueller Electric Company, Inc.

[Home](#) | [Products](#) | [Check Order Status](#) | [About Us](#) | [Contact Us](#) | [Request a Catalog](#) | [Site Map](#)