

main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes
 crocodile clips
 test probes
 oscilloscope test probes
 measuring leads
 plugs
 sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
 sets
 miscellaneous

company

portrait
 corporate association
 location maps
 fairs and exhibitions
 jobs
 imprint
 terms and conditions

Home ▶ sockets ▶ sockets ▶ PKI 10 A

PKI 10 A

datasheet for PKI 10 A
 article number: 930103188



View Full-Size Image



search online catalogue

Search

Search

Messestermine

SPS/IPC/DRIVES
 24. 11. 2016 - 24.
 11. 2016

QR-Code



product description:	order number: 930 103-188
description:	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm.
typ:	PKI 10 A gelb/gruen // yellow/green
system:	4 mm system
order number:	930 103-188
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	unsprung socket Ø 4mm cross hole Ø 2mm
type of termination:	M4 thread
rated voltage:	30 VAC / 60 VDC
rated current:	35 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel
housing material:	PF
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-25 °C to +100 °C
drawing	

