



**Extension Springs Specifications** [CAD Drawings](#) [View/Download](#)

**EI 014B 04 S**

**Ordering Instructions**

Pricing is available for quantities in the range of: 10 - 1000  
For orders over 1000 pieces, add to quote list and we will contact you with pricing.  
For orders less than 10, contact our Customer Service Dept. at 888-SPRINGS (888-777-4647)  
These orders incur a \$20.00 Shipping and Processing Charge per order.

Leave Quantity Field Blank and  
Click **Price Check** to View  
ALL Available Price Breaks  
for This Item

Quantity Required:  **Price Check**

**ADD TO CART**

**Add To Quote List**

**\*\* You must be a registered user to place an order.**

| Specification                                                   |                         |
|-----------------------------------------------------------------|-------------------------|
| Part Number                                                     | EI 014B 04 S            |
| Outside Diameter                                                | 0.094 in                |
| Wire Diameter                                                   | 0.014 in                |
| Maximum Load                                                    | 1.249 lb                |
| Free Length                                                     | 0.625 in                |
| Rate                                                            | 2.83 lb/in              |
| Maximum Length                                                  | 1.015 in                |
| Initial Tension                                                 | 0.141 lb                |
| Material                                                        | SS                      |
| Total Coils                                                     | 33.1                    |
| Number of Coils                                                 | 33.1                    |
| Finish                                                          | PASSIVATE PER ASTM A967 |
| <a href="#">Click Here for Tolerances and Engineering Notes</a> |                         |