


Wiha Combination Wrenches


[SHOP](#)

400 96 Set 15 Piece Metric Combination Wrenches Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit. In Molded tool box

Item No.		OAL			OAL	
		mm	mm		mm	mm
400 96	400 03	7.0	110	400 12	15.0	190
	400 04	8.0	120	400 13	16.0	200
	400 05	9.0	130	400 14	17.0	210
	400 06	10.0	140	400 15	18.0	220
lbs.	400 07	11.0	150	400 16	19.0	230
6.75	400 08	12.0	160	400 17	20.0	240
	400 09	13.0	170	400 18	21.0	250
	400 11	14.0	180			


[SHOP](#)

400 98 Set 18 Piece Metric Combination Wrenches In tool box Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.		OAL			OAL	
		mm	mm		mm	mm
400 98	400 03	7.0	110	400 13	16.0	200
	400 04	8.0	120	400 14	17.0	210
	400 05	9.0	130	400 15	18.0	220
	400 06	10.0	140	400 16	19.0	230
	400 07	11.0	150	400 17	20.0	240
lbs.	400 08	12.0	160	400 18	21.0	250
8.7	400 09	13.0	170	400 19	22.0	260
	400 11	14.0	180	400 20	23.0	270
	400 12	15.0	190	400 27	24.0	280


[SHOP](#)

400 86 Set 9 Piece Metric Combination Wrenches

Made from 31CRV3 high performance tool steel.

Item No.		OAL			OAL	
		mm	mm		mm	mm
400 86	400 03	7.0	110	400 08	12.0	160
	 400 04	8.0	120	400 09	13.0	170
	lbs. 1.3 400 05	9.0	130	400 11	14.0	180
	400 06	10.0	140	400 12	15.0	190
	400 07	11.0	150			


[SHOP](#)

400 88 Set 14 Piece Metric Combination Wrenches Made from 31CRV3 high performance tool steel. Satin chromed sure grip body.

Precision formed for exact fit. In pouch

Item No.		OAL			OAL	
		mm	mm		mm	mm
400 88	400 02	6.0	100	400 09	13.0	170
	400 03	7.0	110	400 11	14.0	180
	 400 04	8.0	120	400 12	15.0	190
lbs.	400 05	9.0	130	400 13	16.0	200
2.3	400 06	10.0	140	400 14	17.0	210
	400 07	11.0	150	400 15	18.0	220
	400 08	12.0	160	400 16	19.0	230


[SHOP](#)

400 94 Set 10 Piece Metric Combination Wrenches

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit. In pouch

Item No.		OAL			OAL	
		mm	mm		mm	mm
400 94	400 06	10.0	140	400 12	15.0	190
	 400 07	11.0	150	400 13	16.0	200
	lbs. 2.3 400 08	12.0	160	400 14	17.0	210
	400 09	13.0	170	400 15	18.0	220
	400 11	14.0	180	400 16	19.0	230