

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300920054](#)
Status: **Active**
Overview: [Slip Rings](#)
Description: Aero-Motive Enclosed Slip Ring, 30A, 10 AWG, 9 Conductors

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19099
UL	E110371
General	
Product Family	Slip Rings
Series	130092
Center Bore Diameter	N/A
Component Type	Enclosed
Current - Maximum per Contact	30.0A
Exclude SD Check	Yes
Mounting Style	Vertical
Number of Conductors	9
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 10
Temperature Range - Operating	-40°C to +120°C
UPC	78678867710
Voltage - Maximum	600V
Wire Size AWG	10
Material Info	
Engineering Number	ISRC39



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130092](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION