



QCPC-6RUVA-BL07F | 1697645

Quareo® Q2000 Series Managed Copper Patch Cord, Category 6 U/UTP, PVC, T568A, 7 ft, blue

- Designed with integrated strain relievers, safeguarding circuit integrity
- Impedance matched for use in Quareo structured cabling systems
- Using Quareo Technology with connection point identification

Body Features

Cable Color	Blue
Shield Style	U/UTP
Boot Type	Flexible strain relief
Cable Construction	PVC stranded
Conductor Material	Copper

Configuration Features

Wiring Pattern	T568A
Keyed	No

Dimensions

Length	2.13 m 7.00 ft
--------	------------------

Industry Standards

Flammability Rating	UL94-V0
Standards Compliance	ANSI/TIA/EIA-968-A CE IEC 60603-7 TICK N355

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
Comments	Standard colors: blue, gray and white (other colors are available upon request) Standard lengths: 4, 7, 10, 15, 25 and 50 feet (other lengths available upon request)

Product Type Features

Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6
Product Type	Cable Assembly
Series	Q2000
System	Managed Connectivity

QCPC-6RUVA-BL07F | 1697645

Usage Conditions

Operating Temperature	-10 – 60 °C 14 – 140 °F
Relative Humidity (Operating)	5%
Relative Humidity (Storage)	5%
Storage Temperature	0 – 50 °C 32 – 122 °F

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant