


KERN MH•CH

Accessories:



Angle bracket,
KERN CH-A03,

Strap, length 375 mm,
width 35 mm,
KERN CH-A04,



Ø 290 mm x 45 mm

Pan beam, approx. 400 g,
beam height 390 mm,
KERN CH-A02,

Tare pan, approx. 300 g,
KERN CH-A01,

The compact one up to 200 kg

KERN HCB
Hanging balance

***DKD**
Certificate
possible

2
Years
Warranty

24
Hours
Delivery

* Delivery period
+ 7 days

STANDARD



Carabine hook
stainless steel standard,
with safety catch.
Aperture 15 mm.
Can be reordered any time,
KERN HCB-A01,

Data hold function
The display can be "frozen"
via the MODE key for
approx. 5 sec



Ready for use
Batteries size AA (3 x 1.5 V)
inclusive. AUTO-OFF func-
tion after 3 min to preserve
the battery. Operation time
approx. 300 h

S-hook
stainless steel, standard.
Aperture approx. 25 mm.
Can be reordered any time,
HCB-A02,

Model	Read- out d g	Weighing- range Max kg	Price € excl. of VAT ex works	OPTION Certificate DKD
KERN				KERN
HCB 20K50	50	20	110,-	963-128
HCB 50K100	100	50	120,-	963-128
HCB 100K200	200	100	140,-	963-129
HCB 200K500	500	200	160,-	963-129

Casing WxDxH 80x45x150 mm. Net weight approx. 400 g.
Total height with carabine and S-hook 290 mm.
LCD display with digit height 12 mm.



INDUSTRIAL BALANCES

