


REVISION CK

DO NOT SCALE
FROM THIS PRINTTABLE 1
(* : CUT TO LENGTH IN FIG 1)
(*** = EXISTING CUSTOMERS ONLY)

SERIES	POSITION	ICA	ICA-H	ICO
-3	06	N/R	N/R	N/R
	08	SBOA-308	ICA-308-V	SBO-308
	10	N/R	N/R	N/R
	12	N/R	N/R	N/R
	14	SBOA-314	ICA-314-V	SBO-314
	16	SBOA-316	ICA-316-V	SBO-316
	18	SBOA-318	ICA-318-V	SBO-318
	20	SBOA-320	ICA-320-V	SBO-320
	22	SBOA-324*	ICA-322-V	SBO-324*
	24	SBOA-324	ICA-324-V	SBO-324
-4	***28	ICA-328-V	ICA-328-V	N/R
	22	SBOA-422	N/R	SBO-422
	24	N/R	N/R	N/R
	10	N/R	N/R	N/R
-6	14	N/R	N/R	N/R
	16	N/R	N/R	N/R
	18	N/R	N/R	N/R
	20	N/R	N/R	N/R
	22	N/R	N/R	N/R
	24	SBOA-624	ICA-624-V	SBO-624
	28	SBOA-628	ICA-628-V	SBO-628
	32	SBOA-632	ICA-632-V	SBO-632
	40	SBOA-640	ICA-640-V	SBO-640
	48	SBOA-648	ICA-648-V	SBO-648
-9	14	N/R	N/R	N/R
	24	N/R	N/R	N/R
	28	N/R	N/R	N/R
	32	N/R	N/R	N/R
	40	N/R	N/R	N/R
	48	N/R	N/R	N/R
	50	N/R	N/R	N/R
	64	N/R	N/R	N/R

* PROPRIETARY NOTE *


THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSMITTED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS ±	TWO PLACE DECIMALS ±	THREE PLACE DECIMALS ±	FOUR PLACE DECIMALS ±	ANGLES ±	IC ASSEMBLY ICX-XXX-XXXX-X
					SHEET 1 OF 2

NOTES:

1. MINIMUM PUSHOUT FORCES:
ICA ASSEMBLY: 5 LBS.
ICE ASSEMBLY: 10 LBS.
ICO ASSEMBLY: 5 LBS.
2. MAXIMUM ALLOWABLE BOW:
.003 [.08] INCH PER INCH.
3. -GG PLATING OPTION NOT AVAILABLE ON SC-2P3-XX OR EZ-1S1-XX.
-GT PLATING OPTION NOT AVAILABLE ON SC-1S1-XX, SC-1P3-XX, OR EZ-1S1-XX,
4. -GG PLATING OPTION AVAILABLE TO EXISTING CUSTOMERS ONLY ON EZ-2P3-XX.
-GT PLATING OPTION AVAILABLE TO EXISTING CUSTOMERS ONLY ON SC-2P3-XX AND EZ-2P3-XX.

FIGURE 1



REF. PART No.	'A'
ICA-322-XXX	1.100 [27.94]
ICO-322-XXX	1.100 [27.94]

MATERIAL:
INSULATOR:
BLACK G.F. POLYESTER
UL RATED 94V-0
SOCKET:
CONTACT: 1/4 HARD BeCu
SHELL: 1/2 HARD BRASS

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: JORDAN 10-29-86
CHECKED BY: FARNSEY 11-10-86

ENG. APPROVAL

ICX-XXX-XXXX-X
SHEET 1 OF 2

TABLE 2 SOCKET SPECIFICATION

LEAD STYLE	'B'	"C"	STANDARD INSERTION FORCE				-L OPTION		LOW INSERTION FORCE (-Z OPTION)			
			ICA	FIG	ICO	FIG	ICA,ICO	FIG	ICA	FIG	ICO	FIG
A	.038 [.96]	.353 [8.97]	SC-6P1-XX	3	SC-6P1-XX	2	N/A		EZ-6P1-XX	3	EZ-6P1-XX	2
B	.038 [.96]	.203 [5.16]	N/A		** SC-1S1-XX	2	N/A		N/A		** EZ-1S1-XX	2
C	.016 [.41]	.165 [4.19]	N/A		SC-8P1-XX	2	N/A		N/A		EZ-8P1-XX	2
E	.038 [.96]	.542 [13.76]	** SC-2P3-XX	3	** SC-2P3-XX		N/A		** EZ-2P3-XX	3	N/A	
F	.008 [.20]	.293 [7.44]	N/A		SC-1P2-XX	3	N/A		N/A		N/A	
H	.038 [.96]	.703 [17.86]	N/A		N/A		N/A		EZ-2P2-XX	3		
J	.038 [.96]	.600 [15.24]	** SC-1P3-XX	3	** SC-1P3-XX	2	N/A		N/A		N/A	
L	.038 [.96]	.230 [5.84]	N/A		SC-3P1-XX	2	N/A		N/A		EZ-3P1-XX	2
M	.028 [.71]	.240 [6.10]	N/A		SC-4P1-XX	2	N/A		N/A		EZ-4P1-XX	2
N	.028 [.71]	.190 [4.83]	N/A		SC-5P1-XX	2	N/A		N/A		EZ-5P1-XX	2
S	.038 [.96]	.300 [7.62]	SC-1P1-XX	3	SC-1P1-XX	2	SC-1L1-GT	4	EZ-1P1-XX	3	EZ-1P1-XX	2
W	.038 [.96]	.703 [17.86]	SC-1W1-XX-1	3	N/A		N/A		EZ-1W1-XX-1	3	N/A	
W2	.038 [.96]	.553 [14.05]	SC-1W1-XX-2	3	N/A		N/A		EZ-1W1-XX-2	3	N/A	
W3	.038 [.96]	.453 [11.51]	SC-1W1-XX-3	3	N/A		N/A		EZ-1W1-XX-3	3	N/A	
PINS TO HAVE 4 FINGER CONTACTS							PINS TO HAVE 6 FINGER CONTACTS					

**SEE NOTES 3 & 4

FIGURE 2 NON-FLUSH ASSY.




FIGURE 3 FLUSH ASSY.




FIGURE 4 -L OPTION





TABLE 4

SERIES	LEAD STYLES	PACKAGING TUBE	PLUG
-3 (ICA)	-A, -B, -C, -F, -L, -M, -S	PT-3-24-01-01	TP-03
-4	-A, -B, -C,	PT-4-24-02-01	TP-03
-6	-F, -L, -M,	PT-6-24-07-01	
-9	-S	PT-9-24-04-01	
		PT-1-24-04-25	
-3	-E, -J, -W, -W2, -W3	PT-3-24-05-01	TP-09
-4	-E, -J, -W, -W2, -W3	PT-1-24-01-121	TP-25
-6	-E, -J, -N, -W, -W2, -W3	PT-6-24-07-01	TP-03
-3	-C, -N	PT-1-24-01-14	TP-03
-3 (ICO)	-A, -B, -C, -F, -L, -M, -S	PT-ICX001	TP-51

⊗ : FILL POSITION WITH SC-1L1-GT
(EZ-1L1-GT FOR -Z OPTION)
(STYLE -S, -Z)

FIGURE 5



NOTCH IN BODY TO BE LOADED IN DIRECTION OF ARROW.
(SEE FIG 5)

TABLE 3

BODY STYLE	"D" REF
ICA	.100
ICO	.050

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSMITTED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.


samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

EXISPROD\ASSEMBLY\DIAP
ICX-ASM2

ICX-XXX-XXXX-X
SHEET 2 OF 2

RECOMMENDED P.C. BOARD LAYOUT FOR ICA .300 OR .600 "S" LEAD STYLE



PLOT SCALE: 1 = .1

samtec

MISC\MKTG\FOOTPRNT
ICA

810 PROGRESS BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147