





FIG. 3
(8 POS ONLY)



P.C.B. HOLE LAYOUT

TOLERANCE $\pm .003$

17 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

800 SERIES — 8 — XX — AX — XXX — D — XXX — LF

POSITIONS —

LF = LEAD FREE

BLANK = MACHINED CONTACT

ES = FORMED CONTACT, GOLD PLATE, NOTE 1



ESL = FORMED CONTACT, LOW GOLD PLATE, 5μIN MAX

D = PC TAIL STANDARD

LSG STYLE AND TAIL CONFIGURATION

AG = INSULATOR

AR = INSULATOR WITH RAILS
(ALMOST RUN THE LENGTH UNDER THE INSULATOR
INSIDE THE CONTACT ROWS, .075 REF HIGH & .045 REF WIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN R BROWN	06MAY04	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS:		CHK K WRIGHT	06MAY04		NAME	DIP SOCKET, 800 SERIES	
INCHES		CHK K WRIGHT	06MAY04				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A1 00779 C=1437539-2				—
—		—		CUSTOMER DRAWING			
				SCALE		1:1	
				SHEET		1 of 4	
				REV		A	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

APPROVED

AD

00

DESCRIPTION

DATE

BY

APPROVED

SEE SHEET 1

-

-

-

800 SERIES MACHINED PREMIUM
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D-LF	5-6437538-4
	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D-LF	9-1437538-5
	W/RAILS						840-AR11D-LF	8-1437538-6
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D-LF	8-1437538-4
	HIGH RETENTION						840-AG34D-LF	8-1437538-3
	HIGH RETENTION						832-AG38D-LF	9-6437533-4
	HIGH RETENTION		.595/.605	.700	1.600	2	832-AG34D-LF	2-6437538-5
	W/RAILS						828-AR12D-LF	6-6437538-9
	W/RAILS		.595/.605	.700	1.400	1	828-AR11D-LF	1-6437538-6
	.180 PC LEAD						828-AG43D-LF	6437538-4
OBSOLETE	HIGH RETENTION						828-AG34D-LF	1-6437538-3
	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-LF	5-6437538-1
	W/RAILS		.595/.605	.700	1.200	1	824-AR11D-LF	9-6437537-9
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D-LF	9-6437537-7
	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D-LF	9-6437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D-LF	9-6437537-5
	HIGH RETENTION						824-AG338D-LF	9-6437537-4
	HIGH RETENTION		.295/.305	.400	1.200	1	824-AG334D-LF	9-6437537-3
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D-LF	7-6437537-3
	HIGH RETENTION						820-AG34D-LF	7-6437537-2
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	.900	1	818-AR44D-LF	4-6437539-9
	W/RAILS						818-AR11D-LF	6-6437537-2
	W/RAILS						816-AR11D-LF	5-6437537-4
	HIGH RETENTION		.295/.305	.400	.800	1	816-AG34D-LF	5-6437537-1
	W/RAILS						814-AR11D-LF	3-6437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG43D-LF	3-6437537-2
	HIGH RETENTION						814-AG34D-LF	3-6437537-1
	W/RAILS		.295/.305	.400	.400	3	808-AR11D-LF	1-6437537-9
	.180 PC LEAD						808-AG43D-LF	6437537-5
	HIGH RETENTION						808-AG34D-LF	6437537-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.	

800 SERIES MACHINED PREMIUM
CONTACT PART NUMBER TABLE

OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D	0-1437538-1
	W/RAILS		.595/.605	.700	1.200	1	824-AR11D	9-1437537-9
	-		.395/.405	.500	1.200	1	824-AG66D	9-1437537-8
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D	9-1437537-7
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG45D	6-1437538-6
	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D	9-1437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D	9-1437537-5
	HIGH RETENTION						824-AG33D	8-1437539-2
	HIGH RETENTION						824-AG338D	9-1437537-4
	HIGH RETENTION						824-AG334D	9-1437537-3
OBSOLETE	-		.295/.305	.400	1.200	1	824-AG32D	9-1437537-2
	-						824-AG31D	8-1437537-9
	-						824-AG30D	8-1437537-7
	-		.395/.405	.500	1.200	1	824-AG14D	8-1437537-6
	-						824-AG12D	8-1437537-5
	-		.595/.605	.700	1.200	1	824-AG11D	8-1437537-2
	-						824-AG10D	8-1437537-1
	-		.295/.305	.400	1.100	1	822-AG11D	7-1437537-8
	-						822-AG10D	7-1437537-7
	W/RAILS						820-AR11D	7-1437537-6
OBSOLETE	.180 PC LEAD						820-AG45D	7-1437537-5
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG44D	7-1437537-4
	.180 PC LEAD						820-AG43D	7-1437537-3
	HIGH RETENTION						820-AG34D	7-1437537-2
	-						820-AG12D	6-1437537-9
	-						820-AG11D	6-1437537-6
	-						820-AG10D	6-1437537-4
	.180 PC LEAD W/RAILS						818-AR44D	4-1437539-9
	W/RAILS						818-AR11D	6-1437537-2
	.180 PC LEAD		.295/.305	.400	.900	1	818-AG44D	6-1437537-1
OBSOLETE	HIGH RETENTION S/B 5-1437537-7						818-AG34D	5-1437538-8
	-						818-AG12D	6-1437537-0
	-						818-AG11D	5-1437537-7
	-						818-AG10D	5-1437537-6
	W/RAILS						816-AR11D	5-1437537-4
	.180 PC LEAD		.295/.305	.400	.800	1	816-AG45D	5-1437537-3
	.180 PC LEAD						816-AG44D	5-1437537-2
	HIGH RETENTION						816-AG34D	5-1437537-1
	HIGH RETENTION						816-AG33D	5-1437537-0
	-						816-AG12D	4-1437537-6
OBSOLETE	-						816-AG11D	4-1437537-0
	-						816-AG10D	3-1437537-7
	.180 PC LEAD, W/RAILS S/B 3-1437537-3						814-AR44D	5-1437533-2
	W/RAILS						814-AR11D	3-1437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG45D	3-1437537-4
	.180 PC LEAD						814-AG44D	3-1437537-3
	.180 PC LEAD						814-AG43D	3-1437537-2
	HIGH RETENTION						814-AG34D	3-1437537-1
	-						814-AG12D	2-1437537-9
	-						814-AG11D	2-1437537-4
OBSOLETE	-						814-AG10D	2-1437537-1
	W/RAILS						808-AR11D	1-1437537-9
	.180 PC LEAD		.295/.305	.400	.400	3	808-AG45D	1-1437537-8
	.180 PC LEAD						808-AG44D	1-1437537-7
	.180 PC LEAD						808-AG43D	1-1437537-5
	HIGH RETENTION						808-AG34D	1-1437537-4
	-						808-AG12D	1-1437537-2
	-						808-AG11D	0-1437537-8
	-						808-AG10D	0-1437537-5
	S/B 6-1437529-8		.295/.305	.400	.300	-	806-AG11D	2-1437533-5
OBSOLETE	SUPERSEDED BY 6-1437529-5						806-AG10D	2-1437533-3
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

WEIGHT -

CUSTOMER DRAWING

SCALE 1:1

SHEET 2 OF 4

REV A3

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

DIP SOCKET,
800 SERIES

1437539-2

AMP 4805 REV 31MAR2000

800 SERIES MACHINED PREMIUM
CONTACT LEAD FREE PART NUMBER TABLE

800 SERIES MACHINED PREMIUM
CONTACT PART NUMBER TABLE

800 SERIES STAMPED ECONOMY
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	W/RAILS	13	.595/.605	.700	2.400	2	848-AR11D-ES-LF	8-1437540-0
OBSOLETE	W/RAILS	14					840-AR12D-ES-LF	6-6447099-8
OBSOLETE	W/RAILS	15					840-AR11D-ESL-LF	7-1437540-2
OBSOLETE	W/RAILS	13	.595/.605	.700	2.000	2	840-AR11D-ES-LF	7-1437540-1
	.180 PC LEAD	15					840-AG44D-ESL-LF	7-1437540-0
OBSOLETE	W/RAILS	15					832-AR11D-ESL-LF	0-6437540-9
OBSOLETE	W/RAILS	13					832-AR11D-ES-LF	0-6437540-8
	.180 PC LEAD	13	.595/.605	.700	1.600	2	832-AG44D-ES-LF	0-6437540-7
	.180 PC LEAD	14					832-AG43D-ES-LF	0-6437540-6
OBSOLETE	.180 PC LEAD W/RAILS	15					828-AR44D-ESL-LF	9-6437539-8
OBSOLETE	W/RAILS	14					828-AR12D-ES-LF	6-6447099-7
OBSOLETE	W/RAILS	13	.595/.605	.700	1.400	1	828-AR11D-ES-LF	9-6437539-6
	.180 PC LEAD	13					828-AG44D-ES-LF	9-6437539-5
OBSOLETE	.180 PC LEAD W/RAILS	15	.295/.305	.400	1.200	1	824-AR47D-ESL-LF	8-6437533-3
OBSOLETE	W/RAILS	13	.295/.305	.400	1.200	1	824-AR31D-ES-LF	8-6437539-7
OBSOLETE	W/RAILS	14	.595/.605	.700	1.200	1	824-AR12D-ES-LF	6-6447099-6
	.180 PC LEAD	15	.595/.605	.700	1.200	1	824-AG44D-ESL-LF	8-6437539-3
	.180 PC LEAD	13	.295/.305	.400	1.100	1	822-AG44D-ES-LF	6-6437539-5
OBSOLETE	W/RAILS	15	.295/.305	.400	1.000	1	820-AR11D-ESL-LF	5-6437539-8
OBSOLETE	W/RAILS	13					820-AR11D-ES-LF	5-6437539-7
OBSOLETE	W/RAILS	15					816-AR11D-ESL-LF	3-6437539-5
OBSOLETE	W/RAILS	13	.295/.305	.400	.800	1	816-AR11D-ES-LF	3-6437539-4
	.180 PC LEAD	15					816-AG44D-ESL-LF	3-6437539-2
OBSOLETE	W/RAILS	13	.295/.305	.400	.700	1	814-AR11D-ES-LF	2-6437539-2
OBSOLETE	W/RAILS	13					808-AR11D-ES-LF	1-6437539-0
	.180 PC LEAD	14	.295/.305	.400	.400	1	808-AG43D-ES-LF	6437537-6
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY
CONTACT PART NUMBER TABLE

17	OBSOLETE	.180 PC LEAD W/RAILS	9	.295/.305	.400	1.200	1	824-AR47D-ESL	8-1437533-3
	SUPERSEDED	.180 PC LEAD W/RAILS S/B 8-1437539-3	9	.595/.605	.700	1.200	1	824-AR44D-ESL	8-1437533-2
	17	W/RAILS	9	.295/.305	.400	1.200	1	824-AR31D-ESL	3-1437540-9
	OBSOLETE	W/RAILS	6					824-AR31D-ES	8-1437539-7
		W/RAILS	7					824-AR12D-ES	6-1447099-6
	OBSOLETE	W/RAILS	9	.595/.605	.700	1.200	1	824-AR11D-ESL	8-1437539-6
	OBSOLETE	W/RAILS	6					824-AR11D-ES	8-1437539-5
	OBSOLETE	-	9	.395/.405	.500	1.200	1	824-AG66D-ESL	8-1437539-4
		17	5					824-AG65D-ES	0-1571180-1
17	OBSOLETE	.180 PC LEAD	9	.595/.605	.700	1.200	1	824-AG44D-ESL	8-1437539-3
		-	7					824-AG32D-ES	8-1437539-1
		-	9					824-AG31D-ESL	7-1437539-7
		-	6	.295/.305	.400	1.200	1	824-AG31D-ES	7-1437539-6
		-	8					824-AG30D-ESL	7-1437539-4
		-	5					824-AG30D-ES	7-1437539-3
		-	7					824-AG12D-ES	7-1437539-2
		-	9	.595/.605	.700	1.200	1	824-AG11D-ESL	7-1437539-0
		-	6					824-AG11D-ES	6-1437539-9
		-	5					824-AG10D-ES	6-1437539-7
	OBSOLETE	.180 PC LEAD	6					822-AG44D-ES	6-1437539-5
		-	7					822-AG12D-ES	6-1437539-4
		-	9	.295/.305	.400	1.100	1	822-AG11D-ESL	6-1437539-3
		-	6					822-AG11D-ES	6-1437539-2
17	OBSOLETE	-	5					822-AG10D-ES	6-1437539-0
	SUPERSEDED	.180 PC LEAD W/RAILS S/B 7-1437537-4	9					820-AR44D-ESL	7-1437533-1
	17	W/RAILS	9					820-AR11D-ESL	5-1437539-8
	OBSOLETE	W/RAILS	6	.295/.305	.400	1.000	1	820-AR11D-ES	5-1437539-7
		.180 PC LEAD S/B 7-1437537-4	9					820-AG44D-ES	7-1437533-0
		-	7					820-AG12D-ES	5-1437539-6
		-	9					820-AG11D-ESL	5-1437539-3
		-	6					820-AG11D-ES	5-1437539-2
		W/RAILS	5					820-AG10D-ES	5-1437539-0
		.180 PC LEAD W/RAILS S/B 4-1437539-9	9					818-AR44D-ESL	6-1437533-4
	OBSOLETE	W/RAILS	9					818-AR11D-ESL	4-1437539-8
	OBSOLETE	W/RAILS	6					818-AR11D-ES	4-1437539-7
		.180 PC LEAD S/B 6-1437537-1	9	.295/.305	.400	.900	1	818-AG44D-ESL	6-1437533-3
		-	7					818-AG12D-ES	4-1437539-6
		-	9					818-AG11D-ESL	4-1437539-4
		-	6					818-AG11D-ES	4-1437539-3
		-	5					818-AG10D-ES	4-1437539-1
	OBSOLETE	W/RAILS	9					816-AR11D-ESL	3-1437539-5
	OBSOLETE	W/RAILS	6					816-AR11D-ES	3-1437539-4
	OBSOLETE	.180 PC LEAD	5	.295/.305	.400	.800	1	816-AG45D-ES	3-1437539-3
		.180 PC LEAD	9					816-AG44D-ESL	3-1437539-2
		-	7					816-AG12D-ES	3-1437539-1
		-	9					816-AG11D-ESL	2-1437539-9
		-	6					816-AG11D-ES	2-1437539-8
		-	5					816-AG10D-ES	2-1437539-6
		.180 PC LEAD, W/RAILS S/B 3-1437537-3	9					814-AR44D-ESL	5-1437533-3
		W/RAILS	9					814-AR11D-ESL	2-1437539-3
	17	W/RAILS	6					814-AR11D-ES	2-1437539-2
	OBSOLETE	.180 PC LEAD	5	.295/.305	.400	.700	1	814-AG45D-ES	2-1437539-1
	SUPERSEDED	.180 PC LEAD S/B 3-1437537-3	9					814-AG44D-ESL	4-1437540-5
		-	7					814-AG12D-ES	2-1437539-0
		-	9					814-AG11D-ESL	1-1437539-7
		-	6					814-AG11D-ES	1-1437539-6
		-	5					814-AG10D-ES	1-1437539-4
		.180 PC W/RAILS, S/B 1437539-9	9					808-AR44D-ESL	3-1437533-1
	OBSOLETE	W/RAILS	9					808-AR11D-ESL	1-1437539-1
		W/RAILS	6					808-AR11D-ES	1-1437539-0
		.180 PC LEAD	9	.295/.305	.400	.400	1	808-AG44D-ESL	0-1437539-9
	OBSOLETE	.180 PC LEAD	7					808-AG43D-ES	1-1437537-6
		-	7					808-AG12D-ES	0-1437539-8
		-	9					808-AG11D-ESL	0-1437539-6
		-	6					808-AG11D-ES	0-1437539-5
		-	5					808-AG10D-ES	0-1437539-2
		S/B 7-1437529-1	7					806-AG12D-ES	2-1437533-8
		S/B 1437535-8	9	.295/.305	.400	.300	1	806-AG11D-ESL	8-1437536-5
		S/B 1437535-7	6					806-AG11D-ES	2-1437533-7
COMMENTS			PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY CONTACT PART NUMBER TABLE													
17	OBSOLETE	-	7	.895/.905	1.000	3.200	2	864-AG12D-ES	5-1437538-3				
		-	9					864-AG11D-ESL	5-1437538-0				
		-	6					864-AG11D-ES	4-1437538-9				
17	OBSOLETE	-	5	.595/.605	.700	2.400	2	864-AG10D-ES	3-1437540-2				
OBSOLETE	W/RAILS	9	848-AR11D-ESL					6-1437540-2					
17	OBSOLETE	W/RAILS	6					848-AR11D-ES	3-1437540-0				
OBSOLETE	-	7	848-AG12D-ES					2-1437540-8					
	-	9	848-AG11D-ESL					4-1437538-2					
	-	6	848-AG11D-ES					2-1437540-6					
17	OBSOLETE	-	5					848-AG10D-ES	2-1437540-5				
	-	9	842-AG11D-ESL					2-1437540-4					
	-	6	842-AG11D-ES					2-1437540-3					
	.180 PC LEAD W/RAILS S/B 2-1437540-0	9	840-AR44D-ESL					0-1437534-7					
17	OBSOLETE	W/RAILS	7	.595/.605	.700	2.000	2	840-AR12D-ES	6-1447099-8				
OBSOLETE	W/RAILS	9	840-AR11D-ESL					2-1437540-2					
OBSOLETE	W/RAILS	6	840-AR11D-ES					2-1437540-1					
	.180 PC LEAD	9	840-AG44D-ESL					2-1437540-0					
	-	7	840-AG12D-ES					1-1437540-9					
	-	9	840-AG11D-ESL					1-1437540-7					
	-	6	840-AG11D-ES					1-1437540-6					
	-	5	840-AG10D-ES					1-1437540-4					
17	OBSOLETE	-	7					.595/.605	.700	1.800	2	836-AG12D-ES	1-1437540-2
	-	9	836-AG11D-ESL									1-1437540-1	
	-	6	836-AG11D-ES	1-1437540-0									
OBSOLETE	W/RAILS	9	832-AR11D-ESL	0-1437540-9									
OBSOLETE	W/RAILS	6	832-AR11D-ES	0-1437540-8									
	.180 PC LEAD S/B 1437540-1	8	832-AG45D-ESL	6-1437538-0									
	.180 PC LEAD S/B 1437540-7	9	832-AG44D-ESL	9-1437533-5									
17	OBSOLETE	.180 PC LEAD	6	.595/.605	.700	1.600	2					832-AG44D-ES	0-1437540-7
OBSOLETE	.180 PC LEAD	7	832-AG43D-ES									0-1437540-6	
	-	7	832-AG12D-ES									0-1437540-5	
	-	9	832-AG11D-ESL					0-1437540-3					
	-	6	832-AG11D-ES					0-1437540-2					
	-	5	832-AG10D-ES					0-1437540-1					
17	OBSOLETE	.180 PC LEAD W/RAILS	9					.595/.605	.700	1.400	1	828-AR44D-ESL	9-1437539-8
OBSOLETE	W/RAILS	7	828-AR12D-ES									6-1447099-7	
OBSOLETE	W/RAILS	9	828-AR11D-ESL									9-1437539-7	
OBSOLETE	W/RAILS	6	828-AR11D-ES									9-1437539-6	
17	OBSOLETE	.180 PC LEAD	6	828-AG44D-ES	9-1437539-5								
	-	7	828-AG12D-ES	9-1437539-4									
	-	9	828-AG11D-ESL	9-1437539-2									
	-	6	828-AG11D-ES	9-1437539-1									
	-	5	828-AG10D-ES	8-1437539-9									
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.					TE PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

DWN R BROWN
CHK K WRIGHT
APVD K WRIGHT
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

DESMAY04
DESMAY04

NAME

SIZE CAGE CODE DRAWING NO
A1 00779

RESTRICTED TO -

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

DIP SOCKET, 800 SERIES

CUSTOMER DRAWING

SCALE 1:1
SHEET 3 OF 4
REV A3


LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					—	SEE SHEET 1	—	—	—

1000 SERIES MACHINED PREMIUM
CONTACT, LOW INSERTION FORCE
PART NUMBER TABLE

S/B 4-1437538-8		.895/.905	1.000	3.200	2	1064-AG11D	2-1437529-4
S/B 3-1437540-1		.895/.905	1.000	3.200	2	1064-AG10D	2-1437529-3
S/B 3-1437538-0		.595/.605	.700	2.000	2	1040-AG11D	2-1437529-2
S/B 2-1437538-2		.595/.605	.700	1.600	2	1032-AG11D	2-1437529-1
S/B 1437538-4		.595/.605	.700	1.400	1	1028-AG11D	1-1437529-9
S/B 8-1437537-9		.295/.305	.400	1.200	1	1024-AG31D	1-1437529-8
S/B 8-1437537-2		.595/.605	.700	1.200	1	1024-AG11D	1-1437529-6
S/B 8-1437537-1		.595/.605	.700	1.200	1	1024-AG10D	1-1437529-5
S/B 6-1437537-6		.295/.305	.400	1.000	1	1020-AG11D	1-1437529-4
S/B 6-1437537-4						1020-AG10D	1-1437529-3
S/B 5-1437537-7		.295/.305	.400	.900	1	1018-AG11D	1-1437529-2
S/B 5-1437537-6						1018-AG10D	1-1437529-1
S/B 4-1437537-0		.295/.305	.400	.800	1	1016-AG11D	1-1437529-0
S/B 3-1437537-7						1016-AG10D	0-1437529-9
S/B 2-1437537-4		.295/.305	.400	.700	1	1014-AG11D	0-1437529-7
S/B 2-1437537-1						1014-AG10D	0-1437529-6
S/B 1437537-8		.295/.305	.400	.400	3	1008-AG11D	0-1437529-5
S/B 1437537-5						1008-AG10D	0-1437529-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

1800 SERIES MACHINED PREMIUM
CONTACT, LOW GOLD
PART NUMBER TABLE

	S/B 5-1437538-0		.895/.905	1.000	3.200	2	1864-AG111D	5-1437529-1
	S/B 6-1437540-2 W/RAILS		.595/.605	.700	2.400	2	1848-AR111D	5-1437529-0
	S/B 4-1437538-2						1848-AG111D	4-1437529-9
	S/B 2-1437540-4		.595/.605	.700	2.100	2	1842-AG111D	4-1437529-8
	S/B 2-1437540-2 W/RAILS		.595/.605	.700	2.000	2	1840-AR111D	4-1437529-7
	S/B 1-1437540-7						1840-AG111D	4-1437529-6
	S/B 1437540-3		.595/.605	.700	1.600	2	1832-AG111D	4-1437529-5
	S/B 9-1437539-7 W/RAILS		.595/.605	.700	1.400	1	1828-AR111D	4-1437529-4
	S/B 9-1437539-2						1828-AG111D	4-1437529-3
	S/B 3-1437540-9 W/RAILS		.295/.305	.400	1.200	1	1824-AR131D	4-1437529-2
OBSOLETE	S/B 8-1437539-6 W/RAILS		.595/.605	.700	1.200	1	1824-AR111D	4-1437529-1
OBSOLETE	S/B 8-1437539-4		.395/.405	.500	1.200	1	1824-AG141D	4-1437529-0
	S/B 7-1437539-7		.295/.305	.400	1.200	1	1824-AG131D	3-1437529-9
	S/B 7-1437539-0		.595/.605	.700	1.200	1	1824-AG111D	3-1437529-8
	S/B 6-1437539-3		.395/.405	.500	1.100	1	1822-AG111D	3-1437529-7
	S/B 5-1437539-8 W/RAILS		.295/.305	.400	1.000	1	1820-AR111D	3-1437529-6
SUPERSEDED	S/B 5-1437539-3						1820-AG111D	3-1437529-5
	S/B 4-1437539-8 W/RAILS		.295/.305	.400	.900	1	1818-AR111D	3-1437529-4
	S/B 4-1437539-4						1818-AG111D	3-1437529-3
OBSOLETE	S/B 3-1437539-5 W/RAILS		.295/.305	.400	.800	1	1816-AR111D	3-1437529-2
	S/B 2-1437539-9						1816-AG111D	3-1437529-1
	S/B 2-1437539-3 W/RAILS		.295/.305	.400	.700	1	1814-AR111D	3-1437529-0
	S/B 1-1437539-7						1814-AG111D	2-1437529-9
	S/B 1-1437539-1 W/RAILS		.295/.305	.400	.400	3	1808-AR111D	2-1437529-6
	S/B 1437539-6						1808-AG111D	2-1437529-5
OBSOLETE	S/B 1437539-8		.295/.305	.400	.300		1806-AG111D	2-1437529-4
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN CHK K WRIGHT	06MAY04 06MAY04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K WRIGHT	06MAY04	NAME	
	0 PLC ± -	PRODUCT SPEC		DIP SOCKET, 800 SERIES	
	1 PLC ± -	APPLICATION SPEC			
MATERIAL -	FINISH -	WEIGHT -	SIZE A1		CAGE CODE 00779
CUSTOMER DRAWING			DRAWING NO 1437539-2		RESTRICTED TO -
			SCALE 1:1		SHEET 4 OF 4
			REV A3		