

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-50-7241

Status:


Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, 24 Circuits



Series

image - Reference only

Documents:

- 3D Model

Packaging Specification PK-2139-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

2139

Application

Power, Wire-to-Board

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

800753619296

Physical

Circuits (maximum)

24

Color - Resin

Natural

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Resin

Nylon

Net Weight

6.144/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm

Temperature Range - Operating

See Product Specification

Material Info

Old Part Number

2139-24C

Reference - Drawing Numbers

Packaging Specification

PK-2139-001

Product Specification

PS-08-50

Sales Drawing

SD-2139

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
2139Series

Use With
2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION