






MATERIALS:

1. GUIDE TRAY - GLASS FILLED POLYBUTYLENE TEREPHTHALATE, STATICALLY DISSIPATIVE, 94V-0, BLACK
2. SHIELD - ZINC DIECAST, CLEAR CHROMATE FINISH
3. DB-9 RECEPTACLE
SHELL: STEEL WITH TIN PLATE
INSULATOR: GLASS FILLED PBT, UL94V-0
CONTACTS: PHOSPHOR BRONZE, 30 MICRO GOLD OVER NICKEL UNDERPLATE
4. ADAPTER CAN BE STACKED SIDE TO SIDE ON A 1.5 INCH MINIMUM SPACING.

WITHOUT SERIAL IDENTIFICATION		73086-0001	
DESCRIPTION		PART NUMBER	
TITLE		REVISE ONLY ON CAD SYSTEM	
GBIC ADAPTER COPPER, DB-9, PASSIVE			
MOLEX INCORPORATED LISLE, ILL. 60532 U.S.A.		SHEET NO. 1 OF 1	DATE 98/05/20
PART NO. SEE CHART		DRWG. NO. SDA-73086-001	
FILE NAME S73086X1.DGN		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	
DIV. D		SIZE B	

MFG. SH. REV.	D	LTR. BY APP'D.	REVISIONS		REMOVE P/N PER UOI 2000-0151 99/08/09 DSL
			DIMENSIONS SHOWN (METRIC) INCH		
			UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
DRWG. BY RKN	CHK'D. BY DLD	1 PLACE ± .010 --- 2 PLACE ± --- ± .25 1 PLACE --- ± ---			
SCALE 2: 1					