


Power Transistors

TO-218 Case*




NPN High Voltage Switching


TYPE NO.	I _C (A)	P _D (W)	BV _{CB0} (V)	BV _{CEO} (V)	V _{CE(SAT)} @ I _C		I _B (mA)	t _{off} (μs)	f _T (MHz)
			MIN	MIN	MAX	MAX		†TYP MAX	†TYP MIN
2N6931**	10	150	350	300	1.0	10	2,000	3.0	---
2N6932**	10	150	450	400	1.0	10	2,000	3.0	---
2N6933**	15	175	450	300	1.0	15	3,000	3.0	---
2N6934**	15	175	550	350	1.0	15	3,000	3.0	---
2N6935**	15	175	650	400	1.0	15	3,000	3.0	---
BU426**	6.0	115	800	375	1.5	2.5	500	4.0	---
BU426A**	6.0	115	900	400	1.5	2.5	500	4.0	---
BU508**	8.0	125	1,000	700	5.0	4.5	2,000	---	7.0†
BU508A**	8.0	125	1,500	700	1.0	4.5	2,000	---	7.0†
BU508D**	8.0	125	1,500	700	1.0	4.5	2,000	---	7.0†
BUV47**	9.0	100	850	400	1.5	6.0	1,200	3.3	---
BUV47A**	9.0	100	1,000	450	1.5	5.0	1,000	3.8	---
BUV48**	15	125	850	400	1.5	10	2,000	3.8	---
BUV48A**	15	125	1,000	450	1.5	8.0	1,600	3.5	---
TIP51**	3.0	100	350	250	1.5	3.0	600	2.0†	2.5
TIP52**	3.0	100	400	300	1.5	3.0	600	2.0†	2.5
TIP53**	3.0	100	450	350	1.5	3.0	600	2.0†	2.5
TIP54**	3.0	100	500	400	1.5	3.0	600	2.0†	2.5

** Available on special order only; please consult factory.

* Devices are also available in TO-247 Case (isolated mounting hole) on special order.



Top View



Bottom View

TO-247 Case

Central[™]
Semiconductor Corp.

■ 1989963 0002438 452 ■

102