

PRODUCT DATASHEET

6 LED Headlight
Energizer
INDUSTRIAL

HDL33AINE

HANDS-FREE

- Light where you need it without having to hold it
- Swivel adjustment aims light



VERSATILE

- Spot, flood and area lights plus night vision LEDs
- Push button switch cycles modes



ECONOMICAL

- Runs 19 hours on one set of batteries in high mode
- LEDs never need replacing



BRIGHT

- Provides 36 lumens of light in high mode
- Uses premium Nichia® LED technology.



Lightweight, versatile and comfortable, the Energizer® Industrial® 6 LED Headlight is perfect for electrical, plumbing, HVAC or other work that requires both hands. It puts light where you are looking and has a swivel adjustment with ratchet positioning for accurate aim.

Variable light sources allow you to choose the best illumination for the job – area, flood, spot or night vision – without changing lights. Also, this light mounts securely to hard hats or can be comfortably worn around the head for long periods of time.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light


Product Detail:

Designation:	Energizer Industrial 6 LED Headlight
Model:	HDL33AINE
Color:	Yellow
Power Source:	Three "AAA"
ANSI/NEDA:	24 Series
Lamp:	6 LEDs - 2 Wh. Spot, 2 Wh. Flood, 2 Red
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	Area - 36, Spot - 25, Flood - 23
Beam Distance (m):	Area - 37, Spot - 35, Flood - 25 2 Red - 16
Peak Beam Intensity (cd):	Area - 350, Spot - 318, Flood - 170 2 Red - 65
Run Time (h:mm):	Area - 19, Spot - 30, Flood - 30 2 Red - 30
Typical Weight:	81 grams (with batteries)
Dimensions (mm):	47 x 72

Performance:

Run Time

Continuous Drain to
End of Useable Light (21°C)



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty

©Energizer / All Rights Reserved