

iglus®

2 options for
all applications

Option 1:

- Without strain relief tiewrap plates



Option 2:


- With strain relief tiewrap plates



- **Quicksnap:** available from stock for 06.016, other widths upon request



- **Quickfix:** with dowel for fast mounting, available from stock for 06.016, other widths upon request



Mounting Brackets: Series 06 "E2 micro"

366 7145
Polymer, One-Piece



Standard



One-piece mounting bracket



Corrosion-resistant



Available pre-assembled




Inner and outer attachment possible



Available with strain relief tiewrap plates


06....1

Moving end



06....2

Fixed end



060.06.12 - 060.20.12: Center bores only

060.30.12 - 060.64.12: Outer bores only

Chain Type

Part No.

Full Set,
with
Tiewrap Plate

Part No. Set

Mounting
Brackets

Number
of Teeth

Dimension
A in mm

Dimension
B in mm

06.06	060.06.12 PZ	060.06.12	1	—	12,5
06.10	060.10.12 PZ	060.10.12	1	—	16,5
06.16	060.16.12 PZ	060.16.12	2	—	22,5
06.20	060.20.12 PZ	060.20.12	2	—	27,0
06.30	060.30.12 PZ	060.30.12	3	22	37,0
06.40	060.40.12 PZ	060.40.12	4	32	47,0
06.50	060.50.12 PZ	060.50.12	5	42	57,0
06.64	060.64.12 PZ	060.60.12	6	56	71,0

06...12 = Full set, each part with pin / bore

06... 1 = Mounting bracket with bore

06... 2 = Mounting bracket with pin

Internet: <http://www.igus.de>
email: info@igus.de