



CIRCUIT BREAKER 230/400V 15KA, 1-POLE,
B, 32A, D=70MM

Similar to image

Technical data:

Overvoltage class		3
type of voltage		AC/DC
Tripping characteristic class		B
Degree of pollution		3
Mounting depth	mm	70
Energy limiting class		3
Number of poles		1
Number of pitch units for width		1
Product function / n-switching		No
Supply voltage frequency / rated value	Hz	50
Breaking capacity current / [nicht versorgt - nach IEC 60947-2] / [nicht versorgt - Bemessungswert]	kA	20
Breaking capacity current / acc. to EN 60898 / rated value	kA	15
Supply voltage / for AC / rated value	V	400
Current / for AC / rated value	A	32
Protection class IP		IP 20
Product extension / can be installed / supplementary device		Yes
power loss	W	2.4

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Global Industry Mall (Online ordering system)


<http://www.siemens.com/lowvoltage/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SY7132-6/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY7132-6



last change:

Dec 21, 2010