

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-52-0127

Status:


Active

Overview:

KK® Interconnect System - Molex

Description:

3.96mm Pitch KK® Crimp Terminal 2878, 18-20 AWG, Bag, Phosphor Bronze, Tin (Sn), Bifurcated



Series

image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-08-50 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	2878
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800754226011

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.165/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20
Wire Size mm²	N/A

Material Info

Old Part Number	2878-B-A-(P909)L
-----------------	------------------

Reference - Drawing Numbers

Product Specification	PS-08-50
Sales Drawing	SD-2878

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2878Series

Use With

2574 , 6422

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimper	0638117500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION