



REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIMENSIONS

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	06/05/03										
7						CHECKED												
6						ISSUED			PART DESCRIPTION									
5	COVER	BRASS	GOLD	1		SMB R/A DIRECT SOLDER PLUG (FOR .085”, .086” SEMI-RIGID CABLE)												
4	INSULATOR	TEFLON	NATURAL	1														
3	CONTACT PIN	BER. COPPER	GOLD	1														
2	INSULATOR	TEFLON	NATURAL	1		SHEET 1 OF 1					PART NO.							
1	BODY	BRASS	GOLD	1							142214							
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE					DWG. NO.		142214.DWG	REV.	A	SIZE	A	SCALE
					C:/142/142214.DWG													