



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ BIL 20

BIL 20

datasheet for BIL 20
article number: 930176103



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 930 176-103	
description:		Socket with insulated head and ring for installation in equipment chassis and switchpanels with a wall thickness up to 2 mm. 4 mm diameter tin-plated brass socket, with solder connection.	
typ:		BIL 20 gelb/yellow	
system:		4mm system	
order number:		930 176-103	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
type of contact:		socket (unsprung)	
type of termination:		M6 thread, solder	
rated voltage:		30 VAC / 60 VDC	
rated current:		32 A	
Please consider derating curve!			
contact resistance:		5 mOhm	
mounting:		screw	
material			
contact material:		brass	
contact surface material:		Tin	
housing material:		PA	
connecting nut material:		brass nickel - plated	
environmental conditions:			
temperature range:		-25 °C to +85 °C	
inflammable class:			
housing (basic material):		UL 94 V - 2	
drawing			
			