

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Spring centre contacts for good electrical contact with large solder bucket.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification
- Attractive body styling
- Maximum cable size 5.5mm

Ratings – 5A at 200 Vdc/150 Vac max

Insulation resistance – 100MΩ at 500 Vdc

Material

Centre contact

Brass

Ground Contact

flash gold plated
Brass,

Insulation

flash gold plated
Noryl SE1

Cable clamp

Brass,



Spring

flash gold finish
Spring steel,

Cap

black chrome plated
Brass,
black chrome plated

Dimensions



CONVERTED FROM PS0362 ISS2 (14.01.94) IN JAN 2003

DrgnNo 342 SERIES

TITLE PROFESSIONAL PHONO LINE SOCKET

ALL DIMENSIONS IN MM
ANGLES IN DECIMAL DEGREES



Delttron Part No	Description
342-0000	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING
342-0100	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (BLACK ID RING)
342-0200	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (BLUE ID RING)
342-0500	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (RED ID RING)
342-0600	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (WHITE ID RING)
342-0700	FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (YELLOW ID RING)

DELTRON *Components*



ISS 2

GENERAL SPECIFICATION
FOR 342 SERIES

CUSTOMER

Aprvd Date 27/01/03

Aprvd By

MC

Drwn by

BFS

Scale: NTS

Sheet 1 / 1